

30mm Command/52, Chrome Finish Heavy Duty, Watertight/Oiltight Complete Metal Unit Non-Illuminated Keyed Selector Switch 4 Position, H-CAM Maintained Lock type 501CH with 2 Keys Key Removal in All Positions with 1 N.O. + 2 N.C. Heavy Duty Contacts, A600/P600 UL Listed, CSA Certified UL File E22655 in Vol. 6 (7) Sec. 13 (2) NEMA 1,3,3R,4,4X,12,13 & Automotive Standards



product brand name	SIEMENS Pilot Devices
design of the product	Complete unit round
Enclosure	
number of command points	1
delivery state as a kit	No
Actuator	
design of the actuating element	Key-operated switch
product extension optional light source	No
color of the actuating element	silver
material of the actuating element	metal
number of contact modules	3
type of unlocking device	key unlatching
number of switching positions	4
switch position for key distraction	removable in every position
lock make	ILLINOIS
key number	501CH
Front ring	
product component front ring	Yes
design of the front ring	standard
material of the front ring	metal
color of the front ring	chrome
Holder	
material of the holder	Metal
General technical data	
product function positive opening	Yes
product component light source	No
insulation voltage rated value	600 V
degree of pollution	1
type of voltage of the operating voltage	AC/DC
surge voltage resistance rated value	4 kV
protection class IP	IP66
• of the terminal	IP20
vibration resistance according to IEC 60068-2-6	0 ... 2000 Hz, 1.52 mm displacement (peak-to-peak) max./ 10g max.
operating frequency maximum	600 1/h
thermal current	10 A
operating voltage	
• at AC at 60 Hz rated value	5 ... 600 V
• at DC rated value	5 ... 600 V
Power Electronics	
contact reliability	one incorrect switching operation of 100 million switching operations (5 V, 1

	mA)
Auxiliary circuit	
number of NC contacts for auxiliary contacts	2
number of NO contacts for auxiliary contacts	1
operational current at AC-15	
• at 110 V rated value	60 A
• at 230 V rated value	30 A
• at 400 V rated value	15 A
• at 500 V rated value	12 A
Connections/ Terminals	
type of electrical connection	screw-type terminals
type of connectable conductor cross-sections for AWG cables for auxiliary contacts	1x (18 ... 12), 2x (18 ... 16), 2x (16 ... 14), 2x 12
tightening torque of the screws in the bracket	20 N·m
tightening torque [lbf·in] with screw-type terminals	8 lbf·in
Safety related data	
touch protection against electrical shock	finger-safe
Ambient conditions	
ambient temperature	
• during operation	-35 ... +70 °C
• during storage	-40 ... +85 °C
Installation/ mounting/ dimensions	
shape of the installation opening	round
Certificates/ approvals	
Further information	

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52SC6HEJ0J1K0>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=US2:52SC6HEJ0J1K0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/US2:52SC6HEJ0J1K0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:52SC6HEJ0J1K0&lang=en

last modified:

12/21/2020 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[52SC6HEJ0J1K0](#)