





**Features**

- Dual isolated GbE LAN ports
- Complies with EN61000-4-5 2kV surge protection
- Complies with IEC 60950-1:2005 + A1: 2009 + A2:2013 2kV HiPOT protection
- Complies with EN61000-4-2 (ESD) Air-15kV, Contact-8kV
- Flexible daughter board with cable to fit into different system
- Industrial temperature -40 °C to 85 °C
- 30μ" golden finger, 3-year warranty
- Industrial design, manufactured in Innodisk Taiwan

**Daughter Board****Mechanical Drawing****Main Board****Specifications**

|                   |                                                                                                                                                                        |
|-------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Form-Factor       | M.2 2242 B-M                                                                                                                                                           |
| Input I/F         | PCI Express 2.1 x 1                                                                                                                                                    |
| Output I/F        | Dual GbE LAN                                                                                                                                                           |
| Output Connector  | RJ45 x 2                                                                                                                                                               |
| TDP               | 2.9W (3.3V x 883mA)                                                                                                                                                    |
| Dimension (WxLxH) | Main board: 22 x 42 x 9.01 mm<br>Daughter board: 50 x 28 x 19.37mm                                                                                                     |
| Temperature       | Operation: STD: 0°C ~ +70°C. W/T: -40°C ~ +85°C<br>Storage: -55°C ~ +95°C                                                                                              |
| Environment       | Vibration: 5G @7~2000Hz, Shock: 50G @ 0.5ms                                                                                                                            |
| Notes             | Please download driver from MyInnodisk website.<br>Windows: XP(32bit), 7(32/64bit), 8/8.1(32/64 bit), 10(32/64bit)<br>Linux: kernel 2.4 series, 2.6.x and 3.x version. |
| Limitations       | EGPL-G202 series does not recommend used in VMware ESXi due to High Latency                                                                                            |

**Headquarters (Taiwan)**

5F., No.237, Sec. 1, Datong Rd.,  
Xizhi Dist., New Taipei City 221,  
Taiwan

Tel: +886-2-7703-3000

Email: sales@innodisk.com

**Branch Offices:****USA**

[usasales@innodisk.com](mailto:usasales@innodisk.com)

+1-510-770-9421

**Europe**

[eusales@innodisk.com](mailto:eusales@innodisk.com)

+31-40-3045-400

**Japan**

[jpsales@innodisk.com](mailto:jpsales@innodisk.com)

+81-3-6667-0161

**China**

[sales\\_cn@innodisk.com](mailto:sales_cn@innodisk.com)

+86-755-21673689

[www.innodisk.com](http://www.innodisk.com)

© 2017 Innodisk Corporation.  
All right reserved. Specifications  
are subject to change without  
prior notice.

December 3, 2020

**Order information**

**EGPL-G202-C1 (Terminal mounting hole, Standard Temp.)**

**EGPL-G202-W1 (Terminal mounting hole , Wide Temp.)**

M.2 to dual isolated GbE LAN module

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Innodisk:

[EGPL-G202-C1](#) [EGPL-G202-W1](#)