

Datasheet

# CFast 3ME4 series

- Exclusive L<sup>3</sup> architecture
- Designed with LDPC ECC engine
- DRAM-less, 100% data integrity
- Excellent random performance
- Wide Temperature: -40°C ~85 °C
- Supports TRIM/NCQ/SMART



## Introduction

Innodisk CFast 3ME4 is characterized by L<sup>3</sup> architecture with the latest SATA III (6.0GHz) Marvell NAND controller. Innodisk's exclusive L<sup>3</sup> architecture is L<sup>2</sup> architecture multiplied LDPC (Low Density Parity Check). L<sup>2</sup> (Long Life) architecture is a 4K mapping algorithm that reduces WAF and features a real-time wear leveling algorithm to provide high performance and prolong lifespan with exceptional reliability. Without additional driver, CFast 3ME4, featured as small form factor, can be configured as a boot device or data storage and is suitable for most industrial application. Supported with hardware write protection, CFast 3ME4 can prevent valuable data on a device from modification and deletion.


Innodisk CFast 3ME4 is designed for industrial field, and supports several standard features, including TRIM, NCQ, and S.M.A.R.T. In addition, Innodisk's exclusive industrial-oriented firmware provides a flexible customization service, making it perfect for a variety of industrial applications.

# CFast 3ME4<sub>series</sub>

## Drawing

**Contact us for more information  
about the CFast 3ME4**

Innodisk is a service-driven provider of industrial embedded flash and DRAM storage products and technologies, with a focus on the cloud computing, industrial/embedded, and aerospace and defense industries.



### Headquarters (Taiwan)

5F., No.237, Sec. 1, Datong Rd.,  
Xizhi Dist., New Taipei City 221,  
Taiwan (R.O.C.)

Tel: +886-2-77033000  
Email: sales@innodisk.com

### Branch Offices:

USA  
[usasales@innodisk.com](mailto:usasales@innodisk.com)  
+1-510-770-9421  
Europe  
[eusales@innodisk.com](mailto:eusales@innodisk.com)  
+31-40-3045-400  
Japan  
[jpsales@innodisk.com](mailto:jpsales@innodisk.com)  
+81-3-6667-0161  
China  
[sales\\_cn@innodisk.com](mailto:sales_cn@innodisk.com)  
+86-755-21673689

[www.innodisk.com](http://www.innodisk.com)

© 2017 Innodisk Corporation.  
All right reserved. Specifications  
are subject to change without  
prior notice.

(General tolerance: ±0.15mm)

## Specifications

Interface	SATA III
Flash Type	MLC
Capacity	8GB~256GB
Max. Channels	2
Sequential R/W (MB/sec, max.)	530/210
Max. Power Consumption	1W
Thermal Sensor	✓
External DRAM Buffer	-
H/W Write Protect	Optional*
ATA Security	✓
S.M.A.R.T.	✓
Dimension (WxLxH)	42.8X 36.4 X 3.6 mm
Environment	Vibration: 20G @7~2000Hz Shock: 1500G @ 0.5ms Storage Temperature: -55°C ~ +95°C MTBF: 3 million hours

## Ordering Information

Operation Temp.	8GB	16GB	32GB	64GB	128GB	256GB
Standard Grade (0°C ~ +70°C)	DECFA-08GM41BC1SC(W)	DECFA-16GM41BC1SC(W) DECFA-16GM41BC1DC(W)	DECFA-32GM41BC1DC(W)	DECFA-64GM41BC1DC(W)	DECFA-A28M41BC1DC(W)	DECFA-B56M41BC1DC(W)
Industrial Grade (-40°C ~ +85°C)	DECFA-08GM41BW1SC(W)	DECFA-16GM41BW1SC(W) DECFA-16GM41BW1DC(W)	DECFA-32GM41BW1DC(W)	DECFA-64GM41BW1DC(W)	DECFA-A28M41BW1DC(W)	DECFA-B56M41BW1DC(W)

\*H/W write protect function is optional.

(For the write protect demand, please place the order by PN: DECFA-xxxM41Bx1xCW)

\*S:Single channel / D: Dual channel

**innodisk**

[www.innodisk.com](http://www.innodisk.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Innodisk:

[DECFA-01TDK1KCAQL](#) [DECFA-64GDK1KCASL](#) [DECFA-A28DK1KCADL](#)