

**Modlink MSDD-set: Frame 4000-68113-0000000,**

insert 4000-68000-0010000

Art.No.: 4000-68113-0010000

Weight: 0.455

Country of origin: US

Model designation: MSDD\_1MV\_VDE MIT LED\_

**[Link to Product](#)**

**Illustration**



Product may differ from Image

0  
0  
0  
0  
0  
0  
0  
0  
0

[illegible]

0  
0  
0  
0  
0  
0  
0  
0  
0  
0

Commercial data	
URL Webshop	<a href="https://shop.murrelektronik.com/4000-68113-0010000">https://shop.murrelektronik.com/4000-68113-0010000</a>
GTIN	4048879036368
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
EAN	4048879036368
Frame	
Material housing	Fine zinc die casting
Coating housing	surface finished
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Germany (VDE)	
Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2

Protection contact present	yes
Connection cross section max.	6 mm <sup>2</sup>
AWG number max.	10
Operating voltage AC	250 V
Operating current	16 A
Status indication LED	yellow

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[4000-68113-0010000](#)