

Modlink MSDD-set: Frame 4000-68122-0000000,

insert 4000-68000-0210000 + 4000-68000-0010000


Art.No.: 4000-68122-0210010

Weight: 0.779

Country of origin: DE

Model designation: MSDD MT. SW 2F.VDE+2X9POL.BU LB67700

[Link to Product](#)**Illustration**

[illegible]

[illegible]

URL Webshop	https://shop.murrelektronik.com/4000-68122-0210010
GTIN	4048879035750
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
EAN	4048879035750

Frame

Material housing	Fine zinc die casting
Coating housing	KTL
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C

Germany (VDE)

Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	yes
Connection cross section max.	6 mm ²
AWG number max.	10
Operating voltage AC	250 V
Operating current	16 A
Status indication LED	yellow

SUB-D9

Family construction form	SUB-D9
Gender	female
No. of poles	9
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D9
Gender Rear	Solder connection
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	3 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42.4 V
Current operating max. (UL)	175 mA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[4000-68122-0210010](#)