



AC Cloud Control

INWFIDAI001I1XX

Wi-Fi interface for Daikin air conditioners

1. Dimensions




Figure 1.1 AC Cloud Control device dimensions in mm

2. Technical Features

| | |
|---|---|
| Enclosure | ABS (UL 94 V-0) |
| Protection | IP20 |
| Dimensions | 34 x 54 x 12 mm |
| Weight | 20g |
| Dimensions (including packaging) | 133 x 135 x 35 mm |
| Weight (including packaging) | 120 g |
| Colour | Light grey NCS S 1002-B |
| Power supply | 12V, 50mA typical Doesn't require external power supply (supplied by the AC Unit) Connection cable supplied |
| Radio Parameters | Wi-Fi 802.11 (b/g/n) RF Frequency band: 2.4 GHz. <i>Consult annex 1 for further information</i> Output power (average): 8 dBm (<i>Modulated signal at antenna chip; 11Mb/Sec.</i>) Bluetooth v4.2 BR/EDR and BLE specification |
| Mounting | Inside or Outside AC unit |
| LED indicators | 1 x Device status |
| Operating Temperature | From 0°C to 70°C |
| Storage temperature | From -20°C to 85°C |
| Operating humidity | 5% to 95% HR, no condensation |
| Storage humidity | <93% HR, no condensation |
| Certifications | CE conformity to EMC directive (2014/53/EU). <ul style="list-style-type: none"> • EN 62368-1:2014 + A11:2020 • AS/NZS 62368.1:2018 • ETSI EN 300 328 V2.2.2 • ETSI EN 303 446-1 V1.2.1 • ETSI EN 301 489-17 V3.2.4 • ETSI EN 301 489-1 V2.2.3 • ETSI EN 301 446-1 V1.2.1 • EN 55032:2015 + AC:2016 + A11:2020 • EN 55035:2017 + A11:2020 • Regulations: FCC/IC Standards: Title 47 CFR Part 15B ICES-003 (Issue 7) |

Table 2.1 Technical features

Annex 1

The device can be configured in 3 different RF Modes:

- USA: 2412 – 2462 MHz (11 channels)
- Europe: 2412 – 2472 MHz (13 channels)
- Japan: 2412 – 2484 MHz (14 channels)

The factory settings are set to work in the most restrictive mode, USA: 2412 – 2462 MHz. Therefore, if the user doesn't change any of these parameters, the gateway is compliant with the most restrictive RF regulations, stricter than European's.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HMS Networks:](#)

[INWFIDAI001I100](#)