

## Defender 4002

### Industrial Security Appliance



The Anybus Defender is an advanced industrial security appliance engineered to provide unparalleled protection for operational technology (OT) networks. Featuring a robust combination of NAT, Routing, Deep Packet Inspection (DPI), and VPN Server and Client functionalities, it serves as a cornerstone for safeguarding critical infrastructure against a myriad of cyber threats.

#### Key use cases:

- **OT/IT Segregation:** Enforce strict policies for domain separation.
- **Address Conflict Avoidance:** Manage IP addresses efficiently through thorough implementation of Network Address Translation (NAT) and routing scenarios.
- **Deep Packet Inspection:** Ensure security of industrial protocols.
- **IEC62443 Compliance:** Implement security zones and conduits according to industry standards for precise machine isolation.
- **Secure Plant-to-Plant OT Connections:** Establish encrypted links between facilities using WireGuard®, OpenSSL, and IPsec Virtual Private Network (VPN) protocols.

### Advanced Router and Firewall

1x WAN and 1x LAN Gigabit Ethernet ports in a Rugged Fan-less IP50 construction for tough environments. Configurable in transparent bridge mode or NAT/Routing mode. Full IPv4 and IPv6 compatible includes DHCP Server, Relay, PPPoE, IGMP Proxy and support for RIPv1 & v2, BGPv4 routing protocols. Supports Rules/policy scheduling and Application and URL whitelisting.



### 3 License options

The Anybus Defender comes pre-configured with one of 3 licensed options to meet your use-cases:




- **NAT/FW:** for network segmentation and translation
- **DPI/FW:** + Virtual Patching of legacy devices and granular Access Control with policy management of industrial protocol transactions
- **PRO/FW:** + Advanced VPN (WireGuard, OpenSSL & IPsec), Traffic shaping and routing functions & high availability capability

### Graphical User Interface [GUI]

Configuration via on board Web interface with use-case wizards for easy configuration. Create rules effortlessly with One-Click Easy Rule creation directly from firewall logs, alongside Floating Rules applicable across all interfaces. Benefit from rich debug and traffic diagnostics capabilities, complemented by an integrated Restful API for seamless integration with higher-level systems. Additionally, gain access to CLI SSH/Console for maintenance tasks.

**Optional:** Central Anybus Cybersecurity Console for management of a group of Defenders.



### Product selection

Article nr:      Description:

ABD4002-NATFW	Industrial Security Appliance - DIN Rail - 2x1Gbit RJ45 - NAT/FW Perpetual License inc. 3Y support
ABD4002-DPIFW	Industrial Security Appliance - DIN Rail - 2x1Gbit RJ45 - DPI/FW Perpetual License inc. 3Y support
ABD4002-PROFW	Industrial Security Appliance - DIN Rail - 2x1Gbit RJ45 - PRO/FW Perpetual License inc. 3Y support

## Defender 4002


### Rich Network Security Controls



Anybus Defenders uphold a Deny by Default policy, ensuring that all network communication traffic is prohibited unless explicitly permitted by the system in both inbound and outbound directions. Simplified NAT Configuration facilitates the setup for single or multiple IP addresses, subnets, or transparent layer 2 firewalling, capable of bridging interfaces and filtering traffic. Enjoy seamless high-throughput Deep Packet Inspection (DPI) for common industrial protocols, supported by an intuitive user interface equipped with auto-learn capabilities to minimize manual rule creation. Integrated of Snort and Suricata, the Defenders offer robust Intrusion Protection capabilities, allowing for virtual patching scenarios. Monitoring and reporting functionalities include Arp and bandwidth monitoring accessible through API. Standard features encompass email reports, syslog integration, and integration with Telegram Messenger as well as Pushover Notifications, while optional NetFlow integration provides additional integration options.

### Asset Discovery & Inventory

The platform incorporates a specialized network asset identification scanner meticulously tailored for OT/ICS devices, offering comprehensive visibility into connected assets. Utilizing a range of industrial-specific protocols and methodologies, it seamlessly discovers, queries, and identifies assets within the network. Extracted information includes crucial details such as make, type, software version, patch level, and serial number, accompanied by an accuracy score for reliability assessment. Accessible through the intuitive Web GUI or centrally propagated to the optional Central Anybus Cybersecurity Console, this information empowers users with actionable insights for enhanced network management and security.



Features License Type	NAT/FW	DPI/FW	PRO/FW
Simple NAT Wizard, 1:1, 1:∞	✓	✓	✓
Stateful Firewall	✓	✓	✓
Transparent/Bridge Mode	✓	✓	✓
Certificate Management	✓	✓	✓
Central Anybus Cybersecurity Console Support	✓	✓	✓
Asset Discovery & Inventory	✓	✓	✓
Email, Syslog, Telegram Messenger and Pushover Notifications	✓	✓	✓
Remote Client VPN		✓	✓
RADIUS, LDAP/AD Authentication		✓	✓
Industrial Protocol DPI with traffic analyser to learn traffic and allow easy config (Ethernet/IP CIP & Modbus)		✓	✓
Virtual Patching through IPS (Snort, Suricata)		✓	✓
WireGuard*, OpenSSL & IPsec VPN		✓	✓
DHCP Server & DHCP Forwarding		✓	✓
Rules/Policy Scheduler (by date/time/duration)		✓	✓
Captive Portal			✓
RIPv1 & v2, BGPv4 routing protocols			✓
Load Balancing, Multi-WAN			✓
Traffic Shaping			✓
High Availability Redundancy			✓

## Defender 4002

### General

Dimensions with connectors	(L x W x H) 114,6 x 118,2 x 64,5 mm / 4,51 x 4,7 x 2,5 inch
Weight	680 gr, 1.5 lbs.
IP rating	IP50 construction
Housing material	Metal enclosure
Mounting	DIN rail according to EN50022
Operating temperature	0°-50°C   32°-122°F
Humidity	Non-Condensing 0%- 85%
Configuration	Via Web interface locally or optional Anybus Cybersecurity Console capable of managing several Defenders simultaneously. CLI SSH/Console access for maintenance tasks.
Certification	CE, 2011/65/EU (RoHS)

### Power

Input voltage	24V DC Power Entry
Current consumption	Max 840 mA @ 24 Volt, 20 Watts (based on maximum ratings)

### Network interfaces

WAN	One (1) RJ45 Gigabit Ethernet
LAN	One (1) RJ45 Gigabit Ethernet

### Software Specifications

Operating Modes	Bridge / Gateway mode
Choice of security license	NAT/FW, DPI/FW, PRO/FW
License type	Perpetual
Warranty	3 years support and warranty included



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HMS Networks:](#)

[ABD4002-NATFW](#) [ABD4002-PROFW](#) [ABD4002-DPIFW](#)