

PTC-Temperature-Sensors

PTC Thermistors, Motor-PTC

Single- and Triplet- Version

Type

YAM

EF1



Applications

- Heavy-duty motors
- electric drives
- mechanical engineering

Benefits

- minimum size
- fast response characteristic
- single-, twin- and triplet- version

Description

PTC-temperature sensors are used for thermal protection of electric machinery and control cabinets, especially electric motors. The structure ensures a fast response time and a simple installation.

The function is obtained by a strong nonlinear PTC effect of the resistor. The usable range is ± 5 K around the nominal temperature. The evaluation is carried out by means of an electronics which detects the sudden increase in resistance and initiates a corresponding action (throttling, shutdown, etc.).

The thermistors are designated according to their nominal response temperature T_{NAT} (°C). Whereas the range below $T_{NAT}-20$ is not defined. Standards for single / triplet PTC thermistors are DIN 44081 / 44082.








Technical data

Description	Dimensions	
	Single thermistor: YAM1, EF1	Triplet thermistor: YAM3
Nominal response temperature	90 °C ... 160 °C (add. 145 °C and 155 °C)	
Maximum allowable operating temp.	170 °C	
Maximum allowable operating voltage	30V	
Resistance R_{25}	$\leq 100 \Omega$	$\leq 300 \Omega$
Resistance at $T_{NAT} - 5$ K	$\leq 550 \Omega$	$\leq 1.650 \Omega$
Resistance at $T_{NAT} + 5$ K	$\geq 1.330 \Omega$	$\geq 3.990 \Omega$
Resistance at $T_{NAT} + 15$ K	$\geq 4.000 \Omega$	$\geq 12.000 \Omega$
Tolerance of T_{NAT}	$\pm 5K$	$\pm 5K$
Dielectric strength	2,5 KV AC	
Connection line	FEP-insulated leads AWG26	
Length of connecting leads	520 mm $\pm$ 10mm	520-180-180-520 mm $\pm$ 10mm

YAM: PTC-pill with shrink tube and epoxy resin

EF1: PTC-pill with screw housing with M4-thread



Versions

type	illustration	drawing dimensions (mm)	technical specification
YAM1			shrink tube and epoxy resin
YAM3			shrink tube and epoxy resin
EF1			screw housing with M4-thread


Identification color (leads)

type	T _{NAT} °C	YAM1, EF1: single-PTC standard ID-color	YAM3: triple-PTC standard ID-color
YAM EF1	90	green-green	green-yellow-yellow-green
	100	red-red	red-yellow-yellow-red
	110	brown-brown	brown-yellow-yellow-brown
	120	gray-gray	gray-yellow-yellow-gray
	130	blue-blue	blue-yellow-yellow-blue
	140	white-blue	white-yellow-yellow-blue
	145	white-black	white-yellow-yellow-black
	150	black-black	black-yellow-yellow-black
	155	blue-black	blue-yellow-yellow-black
	160	blue-red	blue-yellow-yellow-red

Temperature-resistance curve



Ordering example



* Twins or multiple versions (4-fold, 5-fold, 6-fold etc.) possible.
Deviations from the standard generally on request.

Microtherm Sentronic GmbH

Taschenwaldstraße 3
75181 Pforzheim
Deutschland
Tel.: +49 7231 787-0
Fax: +49 7231 787-155
info@microtherm.de
www.microtherm.de



MICROTHERM
sentronic

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Microtherm Sentronic:

[EF1 140 05 500](#) [EF1 180 05 500](#) [EF1 080 05 500](#) [EF1 120 05 500](#) [EF1 150 05 500](#) [EF1 135 05 500](#) [EF1 165 05 500](#) [EF1 155 05 500](#) [EF1 085 05 500](#) [EF1 095 05 500](#) [EF1 170 05 500](#) [EF1 130 05 500](#) [EF1 075 05 500](#) [EF1 125 05 500](#) [EF1 070 05 500](#) [EF1 105 05 500](#) [EF1 145 05 500](#) [EF1 115 05 500](#) [EF1 160 05 500](#) [EF1 110 05 500](#) [EF1 090 05 500](#) [EF1 100 05 500](#) [EF1 175 05 500](#) [YAM1 150 05 520](#) [YAM1 075 05 520](#) [YAM1 085 05 520](#) [YAM2 130 05 520](#) [180 520](#) [YAM1 155 05 520](#) [YAM2 115 05 520](#) [180 520](#) [YAM1 120 05 520](#) [YAM1 130 05 520](#) [YAM2 175 05 520](#) [180 520](#) [YAM1 145 05 520](#) [YAM2 105 05 520](#) [180 520](#) [YAM3 170 05 520](#) [180 180 520](#) [YAM2 170 05 520](#) [180 520](#) [YAM1 160 05 520](#) [YAM3 125 05 520](#) [180 180 520](#) [YAM3 130 05 520](#) [180 180 520](#) [YAM1 115 05 520](#) [YAM1 135 05 520](#) [YAM2 090 05 520](#) [180 520](#) [YAM2 145 05 520](#) [180 520](#) [YAM2 180 05 520](#) [180 520](#) [YAM3 155 05 520](#) [180 180 520](#) [YAM2 160 05 520](#) [180 520](#) [YAM3 075 05 520](#) [180 180 520](#) [YAM3 085 05 520](#) [180 180 520](#) [YAM3 160 05 520](#) [180 180 520](#) [YAM1 070 05 520](#) [YAM1 110 05 520](#) [YAM1 180 05 520](#) [YAM2 150 05 520](#) [180 520](#) [YAM2 155 05 520](#) [180 520](#) [YAM1 095 05 520](#) [YAM2 075 05 520](#) [180 520](#) [YAM3 115 05 520](#) [180 180 520](#) [YAM1 105 05 520](#) [YAM2 080 05 520](#) [180 520](#) [YAM1 080 05 520](#) [YAM1 170 05 520](#) [YAM3 100 05 520](#) [180 180 520](#) [YAM3 135 05 520](#) [180 180 520](#) [YAM2 125 05 520](#) [180 520](#) [YAM1 165 05 520](#) [YAM1 090 05 520](#) [YAM1 125 05 520](#) [YAM2 135 05 520](#) [180 520](#) [YAM3 110 05 520](#) [180 180 520](#) [YAM3 145 05 520](#) [180 180 520](#) [YAM2 140 05 520](#) [180 520](#) [YAM3 070 05 520](#) [180 180 520](#) [YAM2 085 05 520](#) [180 520](#) [YAM3 095 05 520](#) [180 180 520](#) [YAM3 140 05 520](#) [180 180 520](#) [YAM3 150 05 520](#) [180 180 520](#) [YAM1 175 05 520](#) [YAM2 095 05 520](#) [180 520](#) [YAM3 105 05 520](#) [180 180 520](#) [YAM1 100 05 520](#) [YAM2 070 05 520](#) [180 520](#) [YAM2 165 05 520](#) [180 520](#) [YAM3 120 05 520](#) [180 180 520](#) [YAM2 100 05 520](#) [180 520](#) [YAM3 180 05 520](#) [180 180 520](#) [YAM1 140 05 520](#) [YAM2 120 05 520](#) [180 520](#) [YAM3 080 05 520](#) [180 180 520](#) [YAM3 175 05 520](#) [180 180 520](#) [YAM2 110 05 520](#) [180 520](#) [YAM3 090 05 520](#) [180 180 520](#) [YAM3 165 05 520](#) [180 180 520](#)