

Cable drum Ø 355mm

PUR AWG24+22 shielded vt UL/CSA+drag ch. 100m

Art.No.: 7000-C0201-8030000

Weight: 7.623

Country of origin: IT

Model designation: 100m cable 50080919(803) coil 02

Cable drum (100 m)



DeviceNet, CANopen

2× 0.25 + 2× 0.34 mm²

PUR (UL/CSA)

suitable for C-tracks

5 Mio.

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

100m cable 50080919(803) coil 02

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-C0201-8030000
GTIN	4048879337106
ECLASS-6.0	27062011
ECLASS-6.1	27061801
ECLASS-7.0	27061801
ECLASS-7.1	27061801
ECLASS-8.0	27061801
ECLASS-8.1	27061801
ECLASS-9.0	27061801
ECLASS-9.1	27061801
ECLASS-10.0.1	27061801
ECLASS-10.1	27061801
ECLASS-11.0	27061801
ECLASS-11.1	27061801
ECLASS-12.0	27061801
ECLASS-13.0	27061801
ECLASS-14.0	27061801
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444995
EAN	4048879337106
Packaging unit	1

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Installation | Cable

Cable identification	803
Function cable	Hybrid, Data, Power
Amount stranding	2
Stranding	2 wires stranded
Amount stranding (type 2)	1
Stranding (type 2)	2 stranding combinations stranded
Cable shielding (type)	copper braid, tinned
Cable shielding (coverage)	65 %
Banding	Foil
Drain wire (cross-section)	22 AWG
Wire arrangement	(, white, blue,), black, red
Cable weight	63.12 g/m
Material wire insulation	PE
Amount wires	2
Outer diameter insulation	2.1 mm
Outer diameter tolerance core insulation	± 0.05 mm
Shore hardness wire insulation	65 Shore D ± 5 Shore D
Ingredient freeness wire insulation	lead-free, CFC-free, halogen-free
Amount strands (wire)	19
Diameter of single wires	36 AWG
Conductor crosssection (wire)	24 AWG
Drain wire (cross-section)	22 AWG
Material conductor wire	copper stranded wire, tinned

Electrical function wire	Data
Material wire insulation (type 2)	PE
Outer diameter wire insulation (type 2)	2.1 mm
Tolerance outer diameter wire insulation (type 2)	± 0.05 mm
Shore hardness wire insulation (type 2)	65
Ingredient freeness wire insulation (type 2)	lead-free, CFC-free, halogen-free
Amount wires (type 2)	2
Amount strands wire (type 2)	19
Diameter of single wires (type 2)	36 mm
Conductor crosssection wire (type 2)	22 AWG
Material conductor wire (type 2)	copper stranded wire, tinned
Electrical function wire (type 2)	Power
Outer diameter wire insulation (type 3)	1.5 mm
Tolerance outer diameter wire insulation (type 3)	± 0.05 mm
Shore hardness wire insulation (type 3)	65
Amount wires (type 3)	2
Amount strands wire (type 3)	19
Diameter of single wires (type 3)	22 mm
Outer-diameter (jacket)	6.9 mm
Tolerance outer diameter (sheath)	± 5 %
Material jacket	PUR
Shore hardness jacket	89 ± 5 Shore A
Freedom from ingredients (jacket)	lead-free, CFC-free, halogen-free
Conductor resistance (wire)	78 Ω/km @ 20 °C
Conductor resistance (wire type 2)	78 Ω/km @ 20 °C
Conductor resistance (wire type 3)	54 Ω/km @ 20 °C
Electric capacitance	40,000 pF/km
Isolation resistance	5,000 MΩ × km
Nominal voltage AC max.	300 V
Withstand voltage (wire - wire)	2 kV @ 60 s
Withstand voltage (wire - shield)	2 kV @ 60 s
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity min. wire	3 A
Current load capacity min. Wire (type 2)	3 A
Current carrying capacity min. wire (type 3)	6 A
Characteristic impedance	120 Ω ± 10 % @ 10 MHz
Min. operating temperature (static)	-40 °C
Max. operating temperature (fixed)	80 °C
Operating temperature min. (dynamic)	-30 °C
Operating temperature max. (dynamic)	70 °C
Flame resistance	UL 1581 § 1090, UL 1581 § 1100, IEC 60332-1-2
Oil resistance	IEC 60811-404, IRM 901, NEMA WC55
Ozone resistance	IEC 60811-403, EN 50396
UV resistance	UL 1581 § 1200
Other resistances	MUD-resistant (NEK 606), resistant to microbes
Bending radius (fixed)	6 × Outer diameter
Bending radius (dynamic)	10 × Outer diameter
No. of bending cycles (C-track)	1 Mio. @ 25 °C
Traversing distance (C-track)	5 m @ 25 °C
Travel speed (C-track)	3 m/s @ 25 °C
Acceleration (C-track)	5 m/s² @ 25 °C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[7000-C0201-8030000](#)