

TW5354



TW5354 Multi-Constellation Smart Antenna

Overview

The TW5354 is a multi-constellation GNSS Smart Antenna which provides simultaneous GPS/GLONASS+SBAS reception. It is designed for use in professional grade applications such as precision timing, network synchronization, low current applications, and tracking/positioning applications.

The TW5354 GNSS Smart Antenna uses a state of the art multiconstellation GNSS receiver which provides 72 high sensitivity tracking channels which can be configured to acquire and track 3 concurrent GNSS constellations (GPS, Galileo, GLONASS and Beidou) plus SBAS (WAAS, EGNOS, MSAS and GAGAN) and QZSS augmentation signals simultaneously. Differential GPS corrections may also be supplied via RTCM formatted corrections messages.

The TW5354 employs Tallysman's Accutenna™ dual feed antenna patch technology which greatly improves rejection of multi-path signal interference, across the whole GNSS band. The addition of pre- and post- filtering within the RF signal chain greatly improves immunity to jamming carriers typical within urban environments.

The TW5354 can be configured to output a variety of NMEA 0183 message lists with navigation update rates up to 5Hz. An RS422 interface is provided for extended range data communication with input voltage range from 5V to 36V suitable for industrial and Automotive applications.

A configurable one pulse-per-second (1PPS) synchronized to Tallymatics' Windows™ based Configurator enables simple configuration of parameters such as baud rates, output message rates, constellation, tracking parameters and 1PPS configuration and Standby mode parameters.



Features

- Multi-Constellation Receiver/Antenna
- Concurrent tracking of 3 constellations
- 72 Channel simultaneous operation
- High performance tracking (-164 dBm)
- WAAS, EGNOS, MSAS & GAGAN + QZSS
- DGPS corrections using RTCM input
- Navigation rates 1 to 5 Hz
- 1 PPS RS422 outputs
- Accutenna™ Technology
- Pre- and Post- LNA filtering
- Superior multi-path signal rejection
- Industrial grade IP69K enclosure
- RoHS, Reach, RED compliant, CE Marking
- 5V to 36V automotive operation w/ low power standby

TW5354 Smart GNSS Antenna

Specifications

Antenna

Architecture Dual Feed
Axial Ratio < 1 dB typical.
Frequencies GPS/QZSS L1 C/A, GLONASS L1OF
BeiDou B1I, Galileo E1B/C
SBAS WAAS, EGNOS, MSAS, GAGAN
Channels 72-Channel u-blox M8 engine

Interface

Pwr, Gnd
Tx, RX RS422 (30kV protection)
Timepulse RS422 (30kV protection)

Mechanical

Dimensions 66.5 mm dia. x 21 mm H
Weight 135 g
Mounting Method Fixed Mount
Cable Length 5 m with RJ45 termination
Enclosure Industrial grade fixed mount

Electrical

Voltages 5-36 VDC (Overvoltage Protection)
Current <500 mW nominal Operating

Environmental

Operating Temperature -40 C to +85 C
Storage Temperature -45 C to +85 C
Weatherproof IP69K
Shock Vertical axis 50G, other axis 30G
3 axis sweep - 15 min
Vibration 10-200 Hz log sweep 3G

Sensitivity

Tracking & Nav -167 dBm
Cold starts -148 dBm
Hot starts -157 dBm

Acquisition

Cold start 26 sec
Aided 3 sec
Reacquisition 1 sec

Accuracy

Position Accuracy 2.5m CEP (Horizontal)
Velocity Accuracy 0.05 m/s
Heading Accuracy 0.3 deg
Timing Accuracy 30ns RMS

Operational Limits

Dynamics 4 g
Altitude 50,000 m
Velocity 500 m/s

Serial Protocol

Output NMEA 0183
Input RTCM
Baud Rate Configurable up to 230400 bps
Update Rate Configurable up to 5Hz

Time Pulse

Duty Cycle Configurable

Ordering Information:

33-5354-7-yy-zz- PC0 (PC0 = NMEA out, no adaptor cable.)
yy = Radome (00=grey conical, 10=grey low profile, 01=white conical, 11=white low profile)
zz = Cable length in meters. Standard is 5m. (15m and 25m are special order only)

TW5354 SDK Test Adaptor required for programming 33-0095-10

Please refer to the Ordering Guide for the current and complete list of available product options.

About Calian GNSS Ltd.: With global headquarters and manufacturing in Ottawa, Canada, Calian GNSS is a leading manufacturer of high-precision antennas and components for Global Navigation Satellite System (GNSS) applications. Calian GNSS' mission is to support the needs of a new generation of positioning systems by delivering unprecedented antenna precision at competitive prices. Learn more at www.calian.com/GNSS

© 2024 Calian GNSS Ltd. All rights reserved. Calian, the "Confidence. Engineered." tag line and the Calian logo are trademarks or registered trademarks of Calian GNSS Ltd. and/or its affiliates in Canada and certain other countries. All other trademarks mentioned in this document are the property of their respective owners. This document contains Calian proprietary information. Use, disclosure, copying or distribution of information requires the written permission of Calian GNSS Ltd. The information presented is subject to change without notice. Calian assumes no responsibility for any errors or omissions in this document. Calian GNSS Ltd. hereby disclaims any and all warranties and liabilities of any kind.

Contact us:

info.gnss@calian.com
T: +1 613 591-3131

Calian GNSS Ltd.
36 Steacie Drive,
Ottawa ON
K2K 2A9 Canada

www.calian.com/GNSS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Calian:](#)

[33-5262-7-10-05-PC0](#)