

03515SS

DC Axial Fan Sleeve Bearing

35[□]X15^L



General Specifications

Motor Protection Auto Restart / Polarity Protection

Insulation Resistance 10MΩ or over with a DC500V Megger


Dielectric Withstand Voltage : AC700V 1s

Allowable Ambient : - 10℃ ~ +70℃ (Operating)
 Temperature Range - 40℃ ~ +70℃ (Storage)
 non-condensing environment

Expected Life ※ Failure Rate: 10% (L10 Life)


40℃ 30,000 (Hours)

Outline




Panel Out-cuts

(Outlet Side)



Characteristic Curves



Material

- Casing : Plastic (Black) UL94V-0
- Impeller : Plastic (Black) UL94V-0
- Bearing : Sleeve Bearing
- Lead Wire : UL1061 AWG26 + : Red, - : Black

Specifications

Model	Product No.	Rating Voltage	Operating Voltage	Current	Input Power	Speed	Max.Air Flow		Max. Static Pressure		Noise	Mass
		(V)	(V)	(A) ^{*1}	(W) ^{*1}	(min ⁻¹) ^{*1}	(m³/min) ^{*1}	(CFM) ^{*1}	(Pa) ^{*1}	(In H ₂ O) ^{*1}	(dB) ^{*1}	(g)
03515SS-05N-AA-	00	5	4.5 ~ 5.5	0.19	0.95	8000	0.16	5.7	35.0	0.14	24.0	12.5
03515SS-12N-AA-	00	12	6.0 ~ 13.2	0.07	0.84	8000	0.16	5.7	35.0	0.14	24.0	12.5

Rotation: Clockwise as seen from the label side
 Airflow Outlet: Label side

*1: Average Values in Free Air

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[MinebeaMitsumi:](#)

[03515SS-05N-AT-00](#) [03515SS-12N-AT-00](#) [03515SS-05N-AA-00](#) [03515SS-12N-AA-00](#) [03515SS-05N-AL-00](#)
[03515SS-12N-AL-00](#)