

06015SS

DC Axial Fan Sleeve Bearing


60[□]X15^L



General Specifications

- Motor Protection : Auto Restart / Polarity Protection
- Insulation Resistance : 10MΩ or over with a DC500V Megger
- Dielectric Withstand Voltage : AC700V 1s
- Allowable Ambient : -10℃ ~ +70℃ (Operating)
- Temperature Range : -40℃ ~ +70℃ (Storage)
- non-condensing environment

Outline




Expected Life


※ Failure Rate: 10% (L10 Life)

40℃ 40,000 (Hours)

Panel Out-cuts



Characteristic Curves



Material

- Casing : Plastic (Black) UL94V-0
- Impeller : Plastic (Black) UL94V-0
- Bearing : Sleeve Bearing
- Lead Wire : UL1061 AWG26 + : Red, - : Black

Specifications

Model	Product No.	Rating Voltage (V)	Operating Voltage (V)	Current (A)*1	Input Power (W)*1	Speed (min ⁻¹)*1	Max.Air Flow (m³/min)*1	(CFM)*1	Max. Static Pressure (Pa)	(In H ₂ O)	Noise (dB)*1	Mass (g)
06015SS-12L-AA-	00	12	6.0 ~ 13.8	0.08	0.96	3200	0.48	17.0	22.4	0.09	26.0	37
06015SS-12M-AA-	00			0.11	1.32	3700	0.56	19.8	30.8	0.12	30.0	
06015SS-12N-AA-	00			0.17	2.04	4200	0.64	22.6	38.8	0.16	34.0	
06015SS-24L-AA-	00	24	10.0 ~ 26.4	0.05	1.20	3200	0.48	17.0	22.4	0.09	26.0	
06015SS-24M-AA-	00			0.06	1.44	3700	0.56	19.8	30.8	0.12	30.0	
06015SS-24N-AA-	00			0.10	2.40	4200	0.64	22.6	38.8	0.16	34.0	

Rotation: Clockwise as seen from the label side
 Airflow Outlet: Label side
 *1: Average Values in Free Air

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[MinebeaMitsumi:](#)

[06015SS-24N-AT-00](#) [06015SS-12N-AT-00](#) [06015SS-12L-AL-00](#) [06015SS-12M-AL-00](#) [06015SS-24M-AL-00](#)
[06015SS-12L-AT-00](#) [06015SS-24N-AL-00](#) [06015SS-24L-AL-00](#) [06015SS-12M-AT-00](#) [06015SS-24M-AT-00](#)
[06015SS-12N-AL-00](#) [06015SS-24L-AT-00](#)