




OA109AP Dual Voltage



AC Fans - 115, 230V
120mm x 38mm (4.7" x 1.5")




Frame	Die Cast Aluminum, Black Finish	Operating Temperature -20°C ~ +70°C Storage Temperature -40°C ~ +100°C Life Expectancy 80,000 Hours (L10 at 45°C) Weight: 1.2 lbs.	
Impeller	PBT, UL94 V-0 Plastic		
Connection	4x Lead Wires, UL 1430 22 AWG		
Motor	Shaded Pole, Single Phase, Impedance Protected		
Bearing System	Dual Ball Bearings		
Dielectric Strength	1500VAC/min, <1mA		
Insulation Resistance	≥10M Ohm @ 500 VAC		


*60 Hz PQ Airflow Data specifications shown

Part Number	Rated Voltage (Volts AC)	Frequency (Hertz)	Voltage Range (Volts AC)	Input Power (Watts)	Rated Speed (RPM)	Max Airflow (CFM)	Noise Level (dBA)	Max Static Pressure (\"H ₂ O)
OA109AP-11/22-1WB	115 / 230	50 / 60	100-120 200-240	17 / 15	2600 / 3000	90 / 105	42	0.29 / 0.31
OA109AP-11/22-2WB	115 / 230	50 / 60	100-120 200-240	13 / 11	2400 / 2350	77 / 71	35	0.21 / 0.18
OA109AP-11/22-3WB	115 / 230	50 / 60	100-120 200-240	10 / 8	2000 / 1400	66 / 53	27	0.17 / 0.13

Dual Voltage Wiring Diagram 115VAC



Dual Voltage Wiring Diagram 230VAC



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Orion Fans:](#)

[OA109AP-1/2-3WB](#) [OA109AP-1/2-2WB](#) [OA109AP-1/2-1WB](#) [OA109AP-11/22-1WB](#) [OA109AP-11/22-2WB](#)
[OA109AP-11/22-3WB](#) [OA109AP-11/22-2WS](#) [OA109AP-11/22-1WS](#) [OA109AP-11/22-3WS](#) [OA109AP-11/22-1TB](#)
[OA109AP-11/22-2TB](#) [OA109AP-11/22-3TB](#)