

SPPH4 2.2mm-travel Medium-sized Vertical Type

Easy to use mid-size vertical type push switch



Detector

Slide

Push

Rotary


Power

Dual-in-line
Package Type

Horizontal
Type

Vertical
Type

Typical Specifications



Items	Specifications
Rating (max.)/(min.) (Resistive load)	0.1A 30V DC / 50μA 3V DC
Contact resistance (Initial performance)	100mΩ max.
Operating force	2±1N
Operating life with load	10,000 cycles (0.1A 30V DC)

Product Line

Changeover timing	Travel (mm)	Total travel (mm)	Mounting method	Poles	Operation	Terminal type	Location lug	Minimum order unit (pcs.)		Product No.
								Japan	Export	
Non shorting	2.2	3	PC board	2	Latching	Straight	With	1,200	6,000	SPPH410100
					Momentary					SPPH410200
					Latching	Snap-in	Without			SPPH420100
					Momentary		With			SPPH430100
										SPPH430200

Packing Specifications

Bulk

Number of packages (pcs.)		Export package measurements (mm)
1 case / Japan	1 case / export packing	
1,200	6,000	400×270×290


Dimensions

Unit:mm

Style	PC board mounting hole dimensions (Viewed from the direction A)
With boss	

Note Dimensions drawing is for type with location lugs.

Circuit Diagram (Viewed from Direction A)



Terminal Configuration

Unit:mm

Straight terminal	Snap-in terminal

Refer to P.130 for soldering conditions.

Series			Vertical				
			SPEH	SPEJ	SPPH4	SPPH1	
Photo							
Dimensions (mm)	W		6	7	6.5	10	
	D		6	7	8.5	10	
	H		5	5.95	8.5		
Travel (mm)			—	—	2.2	1.5	
Total travel (mm)			1.6	1.7	3	2.5	
Number of poles			1	2			
Operating temperature range			−40℃ to +90℃	−40℃ to +85℃	−10℃ to +60℃		
Automotive use					—		
Life cycle							
Rating (max.) (Resistive load)			50mA 16V DC	0.2A 14V DC	0.1A 30V DC		
Rating (min.) (Resistive load)			10μA 1V DC	—	50μA 3V DC		
Durability	Operating life without load		100,000cycles 400mΩ max.	10,000cycles 150mΩ max.	10,000cycles 100mΩ max.	10,000cycles 40mΩ max.	
	Operating life with load (at max. rated load)		100,000cycles 400mΩ max.	10,000cycles 150mΩ max.	10,000cycles 100mΩ max.	10,000cycles 40mΩ max.	
Electrical performance	Initial contact resistance		200mΩ max.	150mΩ max.	100mΩ max.	20mΩ max.	
	Insulation resistance		100MΩ min. 100V DC	100MΩ min. 500V DC			
	Voltage proof		250V AC for 1minute	500V AC for 1minute			
Mechanical performance	Terminal strength		—	—	5N for 1minute		
	Actuator strength	Operating direction	50N	49N	30N	50N	
		Pulling direction	—	—	10N	—	
Environmental performance	Cold		−40℃ 1000h	−40℃ 500h	−20℃ 96h		
	Dry heat		90℃ 1000h	85℃ 500h	85℃ 96h		
	Damp heat		60℃, 90 to 95%RH 1000h	60℃, 90 to 95%RH 500h	40℃, 90 to 95%RH 96h		
Page			119	120	121	122	


Push Switches Soldering Conditions	130
Push Switches Cautions	131

Note

● Indicates applicability to all products in the series.

Example of Reflow Soldering Condition

1. Heating method: Double heating method with infrared heater.
2. Temperature measurement: Thermocouple ϕ 0.1 to 0.2 CA (K) or CC (T) at soldering portion (copper foil surface).
A heat resisting tape should be used for fixed measurement.
3. Temperature profile



Series (Reflow type)	A (°C) 3s max.	B (°C)	C (s)	D (°C)	E (°C)	F (s)
SPEJ	260	230	40	180	150	120
SPEF						
SPEH						

Notes

1. The condition mentioned above is the temperature on the mounting surface of a PC board. There are cases where the PC board's temperature greatly differs from that of the switch, depending on the PC board's material, size, thickness, etc.
The above-stated conditions shall also apply to switch surface temperatures.
2. Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.

Reference for Hand Soldering

Series	Soldering temperature	Soldering time
SPPJ3, SPPJ2, SPUN, SPUJ, SPPH4, SPPH1	350±10°C	3+1/0s
SPED2, SPED4	350±10°C	3±0.5s
SPEJ	350±10°C	4s max.
SPEF	350±5°C	3s max.
SPEH	350°C max.	3s max.

Reference for Dip Soldering

(For PC board terminal types)

Series	Items		Dip soldering	
	Preheating temperature	Preheating time	Soldering temperature	Duration of immersion
SPPJ3	100°C max.	60s max.	260±5°C	5±1s
SPUN	100°C max.	60s max.	260±5°C	10±1s
SPUJ, SPPH4	—		260±5°C	5±1s
SPPJ2, SPPH1, SPED2, SPED4, SPEF	—		260±5°C	10±1s

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alps Alpine:](#)

[SPPH410100](#) [SPPH410200](#) [SPPH420100](#) [SPPH430200](#) [SPPH430100](#)