

Connectivity Solutions





Table of Contents

M12 Cordsets	4
M12 PUR Cordsets	10
M12 Specialty Cordsets	11
M12 Splitters and Tees	15
Molded I/O Junction Blocks	20
I/O Junction Blocks	22
M12 Power Cordsets	24
M12 Power Junction Blocks	25
M23 Cordsets	26
M8 Cordsets	30
Field Wireable Connectors	34

M12 PVC Cordsets





Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Vibration Shock: Meets IEC 60068-2-6 requirements

Mechanical Shock: Meets IEC 60068-2-27 requirements


Temperature: -40° to +70 °C

Environmental Rating: IP66, IP67, IP68, NEMA 1, UL Type 1




4-Pin (Voltage: 250 V DC/AC, Current: 4 A)




	Length	Straight	Right-Angle	Pinout
4-Pin Female QD to Flying Leads	1 m	BC-M12F4-22-1	BC-M12F4A-22-1	 22 AWG Cable ϕ – 5.2 mm
	2 m	BC-M12F4-22-2	BC-M12F4A-22-2	
	5 m	BC-M12F4-22-5	BC-M12F4A-22-5	
	8 m	BC-M12F4-22-8	BC-M12F4A-22-8	
	10 m	BC-M12F4-22-10	BC-M12F4A-22-10	
	15 m	BC-M12F4-22-15	BC-M12F4A-22-15	




4-Pin Male QD to Flying Leads	1 m	BC-M12M4-22-1	—	 22 AWG Cable ϕ – 5.2 mm
	2 m	BC-M12M4-22-2	—	
	5 m	BC-M12M4-22-5	—	
	8 m	BC-M12M4-22-8	—	
	10 m	BC-M12M4-22-10	—	



	Length	Straight/Straight (Female/Male)	Straight/Right-Angle (Female/Male)	Pinout
4-Pin Double-Ended	0.3 m	BC-M12F4-M12M4-22-0.3	BC-M12F4-M12M4A-22-0.3	 22 AWG Cable ϕ – 5.2 mm
	0.5 m	BC-M12F4-M12M4-22-0.5	—	
	1 m	BC-M12F4-M12M4-22-1	BC-M12F4-M12M4A-22-1	
	2 m	BC-M12F4-M12M4-22-2	BC-M12F4-M12M4A-22-2	
	3 m	BC-M12F4-M12M4-22-3	—	
	4 m	BC-M12F4-M12M4-22-4	—	
	5 m	BC-M12F4-M12M4-22-5	BC-M12F4-M12M4A-22-5	
	6 m	BC-M12F4-M12M4-22-6	—	
	10 m	BC-M12F4-M12M4-22-10	BC-M12F4-M12M4A-22-10	
	15 m	BC-M12F4-M12M4-22-15	BC-M12F4-M12M4A-22-15	



	Length	Straight	Right-Angle	Pinout
4-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	BC-M12F4-22-2-SF	BC-M12F4A-22-2-SF	 22 AWG Cable ϕ – 5.2 mm
	5 m	BC-M12F4-22-5-SF	—	
	10 m	BC-M12F4-22-10-SF	BC-M12F4A-22-10-SF	


*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M12 PVC Cordsets




5-Pin (Voltage: 60 V DC/AC, Current: 4 A)





	Length	Straight	Right-Angle	Pinout
5-Pin Female QD to Flying Leads	1 m	BC-M12F5-22-1	BC-M12F5A-22-1	 <p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p>
	2 m	BC-M12F5-22-2	BC-M12F5A-22-2	
	5 m	BC-M12F5-22-5	BC-M12F5A-22-5	
	8 m	BC-M12F5-22-8	BC-M12F5A-22-8	
	10 m	BC-M12F5-22-10	BC-M12F5A-22-10	
	15 m	BC-M12F5-22-15	—	22 AWG Cable ø – 5.6 mm




5-Pin Male QD to Flying Leads	1 m	BC-M12M5-22-1	—	 <p>Male</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p>
	2 m	BC-M12M5-22-2	—	
	5 m	BC-M12M5-22-5	—	
	8 m	BC-M12M5-22-8	—	
	10 m	BC-M12M5-22-10	—	



	Length	Straight/Straight (Female/Male)	Straight/Right-Angle	Pinout
5-Pin Double-Ended	1 m	BC-M12F5-M12M5-22-1	—	 <p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p>  <p>Male</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p>
	2 m	BC-M12F5-M12M5-22-2	—	
	5 m	BC-M12F5-M12M5-22-5	—	
	8 m	BC-M12F5-M12M5-22-8	—	
	10 m	BC-M12F5-M12M5-22-10	—	



	Length	Straight	Right-Angle	Pinout
5-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	BC-M12F5-22-2-SF	BC-M12F5A-22-2-SF	 <p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p>
	5 m	BC-M12F5-22-5-SF	BC-M12F5A-22-5-SF	
	9 m	BC-M12F5-22-10-SF	BC-M12F5A-22-10-SF	
	15 m	BC-M12F5-22-15-SF	—	


*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M12 PVC Cordsets




8-Pin (Voltage: 30 V DC/AC, Current: 2 A)




	Length	Straight	Right-Angle	Pinout
8-Pin Female to Flying Leads	1 m	BC-M12F8-24-1	—	 <p>Female</p> <p>1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red</p> <p>24 AWG Cable ø – 5.9 mm</p>
	2 m	BC-M12F8-24-2	—	
	5 m	BC-M12F8-24-5	—	
	10 m	BC-M12F8-24-10	—	




	Length	Straight	Right-Angle	Pinout
8-Pin Male to Flying Leads	1 m	BC-M12M8-24-1	—	 <p>Male</p> <p>1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red</p> <p>24 AWG Cable ø – 5.9 mm</p>
	2 m	BC-M12M8-24-2	—	
	5 m	BC-M12M8-24-5	—	
	10 m	BC-M12M8-24-10	—	



	Length	Straight/Straight (Female/Male)	Right-Angle/Straight	Pinout
8-Pin Double-Ended	1 m	BC-M12F8-M12M8-24-1	—	 <p>Female</p> <p>1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red</p> <p>24 AWG Cable ø – 5.9 mm</p>
	2 m	BC-M12F8-M12M8-24-2	—	
	5 m	BC-M12F8-M12M8-24-5	—	
	8 m	BC-M12F8-M12M8-24-8	—	
	10 m	BC-M12F8-M12M8-24-10	—	



	Length	Straight	Right-Angle	Pinout
8-Pin Female QD to Flying Leads Open Shield with Drain Wire	1 m	BC-M12F8-24-1-SF	—	 <p>Female</p> <p>1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red</p> <p>24 AWG Cable ø – 5.6 mm</p>
	2 m	BC-M12F8-24-2-SF	BC-M12F8A-24-2-SF	
	5 m	BC-M12F8-24-5-SF	BC-M12F8A-24-5-SF	
	10 m	BC-M12F8-24-10-SF	BC-M12F8A-24-10-SF	
	15 m	BC-M12F8-24-15-SF	—	

*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

Legacy M12 PVC Cordsets





Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Vibration Shock: Meets IEC 60068-2-6 requirements

Mechanical Shock: Meets IEC 60068-2-27 requirements

Temperature: -40° to +70 °C

Environmental Rating: IP66, IP67, IP68, NEMA 1, UL Type 1



4-Pin (Voltage: 250 V DC/AC, Current: 4 A)



	Length	Straight	Right-Angle		Pinout
4-Pin Female QD to Flying Leads	1 m	MQDC-403	—		1 = Brown 2 = White 3 = Blue 4 = Black
	2 m	MQDC-406	MQDC-406RA		
	3 m	MQDC-410	—		
	5 m	MQDC-415	MQDC-415RA		
	9 m	MQDC-430	MQDC-430RA		
	15 m	MQDC-450	MQDC-450RA		
	18 m	MQDC-460	MQDC-460RA		
	21 m	MQDC-470	MQDC-470RA		
	30 m	MQDC-4100	MQDC-4100RA		
				22 AWG	Cable ϕ – 5.2 mm



4-Pin Male QD to Flying Leads	2 m	MQDMC-406	MQDMC-406RA		1 = Brown 2 = White 3 = Blue 4 = Black
	5 m	MQDMC-415	MQDMC-415RA		
	9 m	MQDMC-430	MQDMC-430RA		
				22 AWG	Cable ϕ – 5.2 mm



	Length	Straight/Straight (Female/Male)	Straight/Right-Angle (Female/Male)		Pinout
4-Pin Double-Ended	0.3 m	MQDEC-401SS	MQDEC-401RS		1 = Brown 2 = White 3 = Blue 4 = Black
	0.6 m	MQDEC-402SS	—		
	0.9 m	MQDEC-403SS	MQDEC-403RS		
	1.8 m	MQDEC-406SS	MQDEC-406RS		
	3.0 m	MQDEC-410SS	—		
	3.6 m	MQDEC-412SS	MQDEC-412RS		
	4.5 m	MQDEC-415SS	—		
	6.1 m	MQDEC-420SS	MQDEC-420RS		
	9.2 m	MQDEC-430SS	MQDEC-430RS		
	15.2 m	MQDEC-450SS	MQDEC-450RS		
				22 AWG	Cable ϕ – 5.2 mm




	Length	Straight	Right-Angle		Pinout
4-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	MQDEC2-406	MQDEC2-406RA		1 = Brown 2 = White 3 = Blue 4 = Black
	5 m	MQDEC2-415	MQDEC2-415RA		
	9 m	MQDEC2-430	MQDEC2-430RA		
	15 m	MQDEC2-450	MQDEC2-450RA		
				22 AWG	Cable ϕ – 5.2 mm

*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.


Legacy M12 PVC Cordsets

5-Pin (Voltage: 60 V DC/AC, Current: 4 A)




	Length	Straight	Right-Angle		Pinout
5-Pin Female QD to Flying Leads	0.9 m	MQDC1-503	—		1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
	2 m	MQDC1-506	MQDC1-506RA		
	5 m	MQDC1-515	MQDC1-515RA		
	9 m	MQDC1-530	MQDC1-530RA		
	18 m	MQDC1-560	—		
	30 m	MQDC1-5100	—		
				22 AWG	Cable \varnothing – 5.6 mm




5-Pin Male QD to Flying Leads	2 m	MQDMC-506	MQDMC-506RA		1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
	5 m	MQDMC-515	MQDMC-515RA		
	9 m	MQDMC-530	MQDMC-530RA		
				22 AWG	Cable \varnothing – 5.6 mm



	Length	Straight/Straight (Female/Male)	Straight/Right-Angle		Pinout
5-Pin Double-Ended	0.3 m	MQDEC-501SS	—		1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
	1 m	MQDEC-503SS	—		
	2 m	MQDEC-506SS	—		
	5 m	MQDEC-515SS	—		
	9 m	MQDEC-530SS	—		
	15 m	MQDEC-550SS	—		
				22 AWG	Cable \varnothing – 5.6 mm











	Length	Straight	Right-Angle		Pinout
5-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	MQDEC2-506	MQDEC2-506RA		1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
	5 m	MQDEC2-515	MQDEC2-515RA		
	9 m	MQDEC2-530	MQDEC2-530RA		
	15 m	MQDEC2-550	MQDEC2-550RA		
	23 m	MQDEC2-575	MQDEC2-575RA		
	30 m	MQDEC2-5100	MQDEC2-5100RA		
				22 AWG	Cable \varnothing – 5.7 mm



*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

Legacy M12 PVC Cordsets

8-Pin (Voltage: 30 V DC/AC, Current: 2 A)

	Length	Straight	Right-Angle		Pinout
 8-Pin Female to Flying Leads	2 m	MQDC1-806	MQDC1-806RA	 Female	1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red
	5 m	MQDC1-815	MQDC1-815RA		
	9 m	MQDC1-830	MQDC1-830RA		
	15 m	MQDC1-850	MQDC1-850RA		
	30 m	MQDC1-8100	—		
 8-Pin Male to Flying Leads	2 m	MQDMC1-806	—	 Male	1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red
	5 m	MQDMC1-815	—		
	9 m	MQDMC1-830	—		
	15 m	MQDMC1-850	—		
 8-Pin Double-Ended	1 m	MQDEC1-803SS	—	 Female	1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red
	2 m	MQDEC1-806SS	—		
	5 m	MQDEC1-815SS	—		
	9 m	MQDEC1-830SS	—		
	15 m	MQDEC1-850SS	—		
	30 m	MQDEC1-8100SS	—		
 8-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	MQDC2S-806	MQDC2S-806RA	 Female	1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red
	5 m	MQDC2S-815	MQDC2S-815RA		
	10 m	MQDC2S-830	MQDC2S-830RA		
	16 m	MQDC2S-850	MQDC2S-850RA		
	31 m	MQDC2S-8100	—		

12-Pin (Voltage: 30 V DC/AC, Current: 2 A)

	Length	Straight	Right-Angle		Pinout
 12-Pin Female to Flying Leads	2 m	MQDC-1206	—	 Female	1 = White 7 = Blue 2 = Brown 8 = Red 3 = Green 9 = Orange 4 = Yellow 10 = Tan 5 = Gray 11 = Black 6 = Pink 12 = Violet
	3 m	MQDC-1210	—		
	5 m	MQDC-1215	—		
	9 m	MQDC-1230	—		

*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M12 PUR Cordsets





Cable: PUR jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Vibration Shock: Meets IEC 60068-2-6 requirements

Mechanical Shock: Meets IEC 60068-2-27 requirements

Temperature: -40° to +70 °C

Environmental Rating: IP66, IP67, IP68, NEMA 1, UL Type 1



4-Pin (Voltage: 250 V DC/AC, Current: 4 A)



	Length	Straight	Right-Angle		Pinout
4-Pin Female QD to Flying Leads	2 m	MQDC-406-PUR	MQDC-406RA-PUR	<p>Female 22 AWG</p>	1 = Brown 2 = White 3 = Blue 4 = Black Cable ø – 4.1 mm
	5 m	MQDC-415-PUR	MQDC-415RA-PUR		
	10 m	MQDC-430-PUR	MQDC-430RA-PUR		



	Length	Straight/Straight (Female/Male)	Right-Angle/Straight (Female/Male)		Pinout
4-Pin Double-Ended	0.3 m	MQDEC-401SS-PUR	MQDEC-401SR-PUR	<p>Female</p>	1 = Brown 2 = White 3 = Blue 4 = Black Cable ø – 4.1 mm
	0.6 m	MQDEC-402SS-PUR	MQDEC-402SR-PUR		
	1 m	MQDEC-403SS-PUR	MQDEC-403SR-PUR		
	2 m	MQDEC-406SS-PUR	MQDEC-406SR-PUR	<p>Male</p>	
	3 m	MQDEC-409SS-PUR	MQDEC-409SR-PUR		
	5 m	MQDEC-415SS-PUR	MQDEC-415SR-PUR		
	10 m	MQDEC-430SS-PUR	MQDEC-430SR-PUR		

*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M12 Specialty Cordsets

Lighted Cordsets

Cable: PVC jacket, translucent white PVC connector body, nickel-plated brass coupling nut





Vibration Shock: Meets IEC 60068-2-6 requirements

Mechanical Shock: Meets IEC 60068-2-27 requirements

Temperature: Max current of 1.0 A: -40 to +60 °C
 Max current of 2.0 A: -40 to +55 °C
 Max current of 4.0 A: -40 to +45 °C

Environmental Rating: IP66, IP67, IP68, NEMA 1, UL Type 1

LED Operation: Green LED indicates power ON; Yellow LED overrides green LED when pin 4 is active



4-Pin (Voltage: 10 to 30 V DC at 15 mA max)



	Length	Straight	Right-Angle		Pinout
4-Pin PNP	2 m	MQDC-406-GYP	MQDC-406-GYPRA	 22 AWG	1 = Brown 2 = White 3 = Blue 4 = Black (ouput LED) Cable ø – 5.2 mm
	5 m	MQDC-415-GYP	MQDC-415-GYPRA		
	9 m	MQDC-430-GYP	MQDC-430-GYPRA		
4-Pin NPN	2 m	MQDC-406-GYN	MQDC-406-GYNRA	 22 AWG	1 = Brown 2 = White 3 = Blue 4 = Black (ouput LED) Cable ø – 5.2 mm
	5 m	MQDC-415-GYN	MQDC-415-GYNRA		
	9 m	MQDC-430-GYN	MQDC-430-GYNRA		

5-Pin (Voltage: 10 to 30 V DC at 15 mA max)



	Length	Straight	Right-Angle		Pinout
5-Pin PNP	2 m	MQDC-506-GYP	MQDC-506-GYPRA	 22 AWG	1 = Brown 2 = White 3 = Blue 4 = Black (ouput LED) 5 = Gray Cable ø – 5.6 mm
	5 m	MQDC-515-GYP	MQDC-515-GYPRA		
	9 m	MQDC-530-GYP	MQDC-530-GYPRA		
5-Pin NPN	2 m	MQDC-506-GYN	MQDC-506-GYNRA	 22 AWG	1 = Brown 2 = White 3 = Blue 4 = Black (ouput LED) 5 = Gray Cable ø – 5.6 mm
	5 m	MQDC-515-GYN	MQDC-515-GYNRA		
	9 m	MQDC-530-GYN	MQDC-530-GYNRA		

M12 Specialty Cordsets

Coiled Cordsets



Cable: PUR jacket, black PUR connector body, nickel-plated brass coupling nut

Vibration Shock: Meets IEC 60068-2-6 requirements

Mechanical Shock: Meets IEC 60068-2-27 requirements

Temperature: -40° to +70 °C

Environmental Rating: IP67, IP69K, NEMA 1, 3, 4, 6P, 13



4-Pin (Voltage: 250 V DC/AC, Current: 4 A)



	Length (retracted to extended)	Straight	Pinout
4-Pin	0.8 to 1.7 m	MQDC-401.7M-PUR-C	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black</p> <p>22 AWG Cable ø – 5.2 mm</p>
	1.0 to 2.6 m	MQDC-402.6M-PUR-C	
	1.2 to 3.3 m	MQDC-403.3M-PUR-C	



	Length (retracted to extended)	Straight/Straight	Pinout
4-Pin Double-Ended	0.8 to 1.7 m	MQDEC-401.7M-PUR-C	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black</p> <p>22 AWG Cable ø – 5.2 mm</p>
	1.0 to 2.6 m	MQDEC-403.3M-PUR-C	

M12 Specialty Cordsets

High Pressure and Temperature Washdown Cordsets

Cable: PVC jacket, 316 stainless steel nut


Vibration Shock: Meets IEC 60068-2-6 requirements

Mechanical Shock: Meets IEC 60068-2-27 requirements

Temperature: -40 to +70 °C

Environmental Rating: IP66, IP67, IP68, IP69K, NEMA 1, UL Type 1

Certifications: **ECOLAB** test F and E Nr. 40-1



4-Pin (Voltage: 250 V DC/AC, Current: 4 A)



	Length	Straight	Pinout
4-Pin	2 m	MQDC-WDSS-0406	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black</p> <p>22 AWG Cable ϕ - 4.8 mm</p>
	5 m	MQDC-WDSS-0415	
	9 m	MQDC-WDSS-0430	



	Length	Straight/Straight	Pinout
4-Pin Double-Ended	0.31 m	MQDEC-WDSS-401SS	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black</p>
	0.91 m	MQDEC-WDSS-403SS	
	1.83 m	MQDEC-WDSS-406SS	<p>Male</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black</p> <p>22 AWG Cable ϕ - 4.8 mm</p>
	3.7 m	MQDEC-WDSS-412SS	

5-Pin (Voltage: 60 V DC/AC, Current: 4 A)



	Length	Straight	Pinout
5-Pin	2 m	MQDC-WDSS-0506	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p> <p>22 AWG Cable ϕ - 5.2 mm</p>
	5 m	MQDC-WDSS-0515	
	9 m	MQDC-WDSS-0530	



	Length	Straight/Straight	Pinout
5-Pin Double-Ended	1.5 m	MQDEC-WDSS-505SS	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p>
	3 m	MQDEC-WDSS-510SS	
	4.57 m	MQDEC-WDSS-515SS	<p>Male</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p> <p>22 AWG Cable ϕ - 4.8 mm</p>

M12 Specialty Cordsets

Chemical Washdown Cordsets


Cable: White polypropylene jacket, polypropylene connector body, polypropylene contact carriers, 316 stainless steel nut

Vibration Shock: Meets IEC 60068-2-6 requirements

Mechanical Shock: Meets IEC 60068-2-27 requirements

Temperature: -40 °C to +90 °C

Environmental Rating: IP68, NEMA 1, 3, 4, 6P



5-Pin (Voltage: 250 V DC/AC, Current: 4 A)



	Length	Straight	Pinout
5-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	MQDCWD-506	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p> <p>22 AWG Cable ϕ – 4.5 mm</p>
	9 m	MQDCWD-530	

Namur



Cable: Blue PVC jacket, PUR connector body, nickel-plated brass coupling nut

Vibration Shock: Meets IEC 60068-2-6 requirements


Mechanical Shock: Meets IEC 60068-2-27 requirements

Temperature: -40 °C to +105 °C

Environmental Rating: IP67, NEMA 1, 3, 4, 6P, 13



4-Pin (Voltage: 250 V DC/AC, Current: 4 A)



	Length	Straight	Right-Angle	Pinout
4-Pin	2 m	MQD9-406	MQD9-406RA	<p>Female</p> <p>1 = Brown 2 = Blue</p> <p>20 AWG Cable ϕ – 5.2 mm</p>
	5 m	MQD9-415	MQD9-415RA	
	9 m	MQD9-430	MQD9-430RA	


M12 Splitters and Tees

Round QD Splitters


Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Temperature: -40 to +90 °C


Environmental Rating: IP68




Example of Parallel 4-Pin Wiring



S15YA24-M124-M124-0.2M
Non-parallel 4-Pin Wiring



S15YA4-M124-M124-0.2M
Non-parallel 4-Pin Wiring



4-Pin (Voltage: 60 V DC/AC, Current: 2 A)



	Models	Cable Lengths		Pinout
		Trunk (Male)	Branches (Female)	
4-Pin	CSRB-M1240M1241	No Trunk/ Integral QD	0.3 m	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black</p>
	CSRB-M1240M1242		0.6 m	
	CSRB-M1240M1243		0.9 m	
	CSRB-M1240M1244		1.2 m	
4-Pin	S15YA24-M124-M124-0.2M	No Trunk/ Integral QD	0.2 m	<p>Male</p> <p>4 x 22 AWG Cable ø – 5.5 mm</p>
	S15YA4-M124-M124-0.2M			
	S15YB-M124-M124-0.2M			

5-Pin (Voltage: 60 V DC/AC, Current: 2 A)



	Models	Cable Lengths		Pinout
		Trunk (Male)	Branches (Female)	
5-Pin	CSRB-M1250M125.47M125.73	No Trunk/ Integral QD	Branch 1 0.14 m Branch 2 0.22 m	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gn/Ye</p> <p>Male</p> <p>5 x 22 AWG Cable ø – 5.5 mm</p>

M12 Splitters and Tees



Compact Flat QD Splitters and Tees

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Temperature: -40 to +90 °C

Environmental Rating: IP68

Example of Parallel 4-Pin Wiring



4-Pin (Voltage: 250 V DC/AC, Current: 4 A)



	Models	Dimensional Drawing	Pinout
4-Pin	CSB-M1240M1240	Figure A	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black</p> <p>Male</p> <p>22 AWG Cable ø – 6.0 mm</p>

5-Pin (Voltage: 30 V DC/AC, Current: 2 A)



	Models	Dimensional Drawing	Pinout
5-Pin	CSB-M1250M1250-T	Figure C	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p> <p>Male</p> <p>22 AWG Cable ø – 5.5 mm</p>
	CSB-M1250M1250A	Figure A	
	CSB-M1250M1250	Figure B	

8-Pin (Voltage: 60 V DC/AC, Current: 2 A)



	Models	Dimensional Drawing	Pinout
8-Pin	CSB-M1280M1280	Figure A	<p>Female</p> <p>1 = Brown 2 = Or/Bk 3 = Orange 4 = White 5 = Black 6 = Blue 7 = Gr/Ye 8 = Violet</p> <p>Male</p> <p>22 AWG Cable ø – 6.0 mm</p>

M12 Splitters and Tees




Flat QD Splitters

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Temperature: -40 to +90 °C

Environmental Rating: IP68

Example of Parallel 4-Pin Wiring



4-Pin (Voltage: 250 V DC/AC, Current: 4 A)



	Models	Cable Lengths		Pinout
		Trunk (Male)	Branches (Female)	
4-Pin	CSB-M1240M1241	No Trunk/Integral QD	2 x 0.3 m	<p>1 = Brown 2 = White 3 = Blue 4 = Black</p> <p>22 AWG Cable ø – 6.0 mm</p>
	CSB-M1241M1241	0.3 m	2 x 0.3 m	
	CSB-M1243M1243	1 m	2 x 1 m	
	CSB-M1248M1241	2.4 m	2 x 0.3 m	
	CSB-M12415M1241	4.6 m	2 x 0.3 m	
	CSB-UNT425M1241	7.6 m Unterminated	2 x 0.3 m	

5-Pin (Voltage: 30 V DC/AC, Current: 2 A)



	Models	Cable Lengths		Pinout
		Trunk	Branches	
5-Pin	CSB-M1251M1251B	0.3 m (Male)	2 x 0.3 m (Female)	<p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p> <p>22 AWG Cable ø – 5.9 mm</p>
	CSB-M1251FM1251M	0.3 m (Female)	2 x 0.3 m (Male)	

8-Pin (Voltage: 60 V DC/AC, Current: 2 A)



	Models	Cable Lengths		Pinout
		Trunk (Male)	Branches (Female)	
8-Pin	CSB-M1281M1281B	0.3 m	2 x 0.3 m	<p>1 = Brown 2 = Or/Bk 3 = Orange 4 = White 5 = Black 6 = Blue 7 = Gr/Ye 8 = Violet</p> <p>22 AWG Cable ø – 6.0 mm</p>

M12 Splitters and Tees




Wiring Splitters

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut




Temperature: -40 to +105 °C

Environmental Rating: IP68

Example of 4-Pin Wiring



4-Pin (Voltage: 250 V DC/AC, Current: 4 A)

	Models	Cable Lengths		Pinout
		Trunk (Male)	Branches (Female)	
 4-Pin	CSA-M1240M1241	No Trunk/ Integral QD	2 x 0.3 m	 Female 1 = Brown 2 = White 3 = Blue 4 = Black  Male
	CSA-M1240M1243	No Trunk/ Integral QD	2 x 1 m	
	CSA-M1240M1246	No Trunk/ Integral QD	2 x 2 m	
	CSA-M1241M1241	0.3 m	2 x 0.3 m	
	CSA-M1243M1243	1 m	2 x 1 m	
	CSA-M1246M1246	2 m	2 x 2 m	
				22 AWG Cable ø – 6.0 mm


M12 Multi-port Splitters

Multi-port Splitters


Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Temperature: -40° to +90 °C

Environmental Rating: IP68



Example of Parallel 5-Pin Wiring (diagram applies to all branches)



5-Pin (Voltage: 30 V DC/AC, Current: 2 A)





Models	Cable Lengths		Pinout
	Branches (Female)	Trunk (Male)	
5-Pin	CSB4-M1251M1250	4 x No Branch / Integral QD	0.3 m
			<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black</p> <p>Male</p> <p>4 x 22 AWG Cable ø – 5.6 mm</p>


M12 Molded Junction Blocks

Temperature: -40 to +70 °C

Environmental Rating: IP65, IP67, and IP68





Example of Parallel 5-Pin Wiring
(diagram applies to all branches)



5-Pin (Voltage: 30 V DC/AC, Current: 2 A)




	Models	Cable Lengths		Pinout
		Branches (Female)	Trunk (Male)	
5-Pin	R50-4M125-M125Q-P	4 x No Branch/ Integral QD	No Trunk/Integral QD	 <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p>
	R95-8M125-M125Q-P	8 x No Branch/ Integral QD	No Trunk/Integral QD	


Molded I/O Junction Blocks

Temperature: -40 to +70 °C

Environmental Rating: IP67



Wiring Diagram



5-Pin (Voltage: 30 V DC/AC, Current: 2 A)


Models	Cable Lengths		Pinout
	Branches (Female)	Trunk	
R95-8M125-C1-D24P		1 m with Flying Leads	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p> <p>Male</p> <p>1 = Purple 2 = Red 3 = Gray 4 = Red/Blue 5 = Green 6 = Blue (18 AWG) 7 = Gray/Pink 8 = White/Green 9 = White/Yellow 10 = White/Gray 11 = Black 12 = Green/Yellow (18 AWG) 13 = Yellow/Brown 14 = Brown/Green 15 = White 16 = Yellow 17 = Pink 18 = Gray/Brown 19 = Brown (18 AWG)</p> <p>18 and 22 AWG Cable ø – 9.2 mm</p>
R95-8M125-0.3M23-D24P		0.3 m 19-pin M23 Male QD	
R95-8M125-C1-D24	8 x No Branch/ Integral QD	1 m with Flying Leads	
R95-8M125-0.3M23-D24		0.3 m 19-pin M23 Male QD	




M8 I/O Junction Blocks

Temperature: -25 to +80 °C

Environmental Rating: IP67




Wiring Diagram




4 Port 3-Pin (Voltage: 120 V DC/AC, Current: 2 A)



	Models	Output	Pinout
3-Pin to 8-Pin	JB-4M8-M12-P4	PNP	<p>Female</p> <p>1 = Brown 3 = Blue 4 = Black</p>
	JB-4M8-M12-N4	NPN	<p>Male</p> <p>1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red</p>
	JB-4M8-M12-4	Discrete	



Wiring Diagram



8 Port 3-Pin (Voltage: 120 V DC/AC, Current: 2 A)




	Models	Output	Pinout
3-Pin to 12-Pin	JB-8M8-M12-P4	PNP	<p>Female</p> <p>1 = Brown 3 = Blue 4 = Black</p>
	JB-8M8-M12-N4	NPN	<p>Male</p> <p>1 = White 7 = Blue 2 = Brown 8 = Red 3 = Green 9 = Orange 4 = Yellow 10 = Tyrian Purple 5 = Gray 11 = Black 6 = Pink 12 = Violet</p>
	JB-8M8-M12-4	Discrete	



M12 I/O Junction Blocks

Temperature: -25 to +80 °C

Environmental Rating: IP67






Wiring Diagram





4 Port 5-Pin (Voltage: 120 V DC/AC, Current: 2 A)



Models	Output	Pinout
JB-4M12-M23-P24	PNP	 <p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p>  <p>Male</p> <p>1 = White 7 = Blue 2 = Brown 8 = Red 3 = Green 9 = Orange 4 = Yellow 10 = Tyrian Purple 5 = Gray 11 = Black 6 = Pink 12 = Violet</p>
JB-4M12-M23-N24	NPN	
JB-4M12-M23-24	Discrete	





Wiring Diagram



8 Port 5-Pin (Voltage: 120 V DC/AC, Current: 2 A)




Models	Output	Pinout
JB-8M12-M23-P24	PNP	 <p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p>  <p>Male</p> <p>1 = Purple 11 = Black 2 = Red 12 = Green/Yellow (18 AWG) 3 = Gray 13 = Yellow/Brown 4 = Red/Blue 14 = Brown/Green 5 = Green 15 = White 6 = Blue (18 AWG) 16 = Yellow 7 = Gray/Pink 17 = Pink 8 = White/Green 18 = Gray/Brown 9 = White/Yellow 19 = Brown (18 AWG) 10 = White/Gray</p>
JB-8M12-M23-N24	NPN	
JB-8M12-M23-24	Discrete	

M12 Power Cordsets

Cable: Shielded PVC jacket with black TPU overmolding, nickel-plated brass coupling nut, gold-plated brass terminal

Temperature: Fixed installation: -40 °C to +85 °C , flexible installation: -25 °C to +85 °C

Environmental Rating: IP67, IP68



5-Pin L-Code (Voltage: 63 V DC/AC, Current: 16 A)



	Length	Straight		Pinout
5-Pin Female QD to Flying Leads	1 m	BCP-M12LF5-14-1		1 = Brown 2 = White 3 = Blue 4 = Black 5 = Yellow/Green Shell = Braid
	2 m	BCP-M12LF5-14-2		
	5 m	BCP-M12LF5-14-5		
	10 m	BCP-M12LF5-14-10		
	15 m	BCP-M12LF5-14-15		
	20 m	BCP-M12LF5-14-20		
			14 AWG	Cable \varnothing – 9.6 mm



5-Pin Male QD to Flying Leads	1 m	BCP-M12LM5-14-1		1 = Brown 2 = White 3 = Blue 4 = Black 5 = Yellow/Green Shell = Braid
	2 m	BCP-M12LM5-14-2		
	5 m	BCP-M12LM5-14-5		
	10 m	BCP-M12LM5-14-10		
	15 m	BCP-M12LM5-14-15		
	20 m	BCP-M12LM5-14-20		
			14 AWG	Cable \varnothing – 9.6 mm




	Length	Straight/Straight (Female/Male)		Pinout
5-Pin Double-Ended	1 m	BCP-M12LF5-M12LM5-14-1		1 = Brown 2 = White 3 = Blue 4 = Black 5 = Yellow/Green Shell = Braid
	2 m	BCP-M12LF5-M12LM5-14-2		
	5 m	BCP-M12LF5-M12LM5-14-5		
	10 m	BCP-M12LF5-M12LM5-14-10		
	15 m	BCP-M12LF5-M12LM5-14-15		
	20 m	BCP-M12LF5-M12LM5-14-20		
			14 AWG	Cable \varnothing – 9.6 mm


M12 Power Junction Blocks

Temperature: -40 °C to +70 °C

Environmental Rating: IP67



Example of 4-Pin Wiring



5-Pin L-Code (Voltage: 60 V DC, Current: 16 A)




Models	Cable Lengths		Pinout
	Branches (Female)	Trunk (Male)	
R50-2M125L-M125-P	2 x No Branch/ Integral QD (in-line)	No Trunk/Integral QD	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Yellow/Green Shell = Braid</p> <p>Male</p>
R50T-2M125L-M125-P	2 x No Branch/ Integral QD (tee)	No Trunk/Integral QD	

M23 PVC Cordsets

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Temperature: -25° to +85 °C

Environmental Rating: IP67 and IP68



19-Pin (Voltage: 150 V DC/AC, Current: 8 A (18 gauge), 2A (22 gauge))



	Length	Straight		Pinout
19-Pin Female QD to Flying Leads	1 m	BC-M23F19-1822-1		1 = Purple
	2 m	BC-M23F19-1822-2		2 = Red
	5 m	BC-M23F19-1822-5		3 = Gray
	10 m	BC-M23F19-1822-10		4 = Red/Blue
	15 m	BC-M23F19-1822-15		5 = Green
	20 m	BC-M23F19-1822-20		6 = Blue (18 AWG)
			7 = Gray/Pink	8 = White/Green
			9 = White/Yellow	10 = White/Gray
			11 = Black	12 = Green/Yellow (18 AWG)
			13 = Yellow/Brown	14 = Brown/Green
			15 = White	16 = Yellow
			17 = Pink	18 = Gray/Brown
			19 = Brown (18 AWG)	
			18 and 22 AWG	Cable ø – 9.8 mm



	Length	Straight		Pinout
19-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	BC-M23F19-1822-2-SFP		1 = Purple
	5 m	BC-M23F19-1822-5-SFP		2 = Red
	10 m	BC-M23F19-1822-10-SFP		3 = Gray
			4 = Red/Blue	5 = Green
			6 = Blue (18 AWG)	7 = Gray/Pink
			8 = White/Green	9 = White/Yellow
			10 = White/Gray	11 = Black
			12 = Green/Yellow (18 AWG)	13 = Yellow/Brown
			14 = Brown/Green	15 = White
			16 = Yellow	17 = Pink
			18 = Gray/Brown	19 = Brown (18 AWG)
			18 and 22 AWG	Cable ø – 9.8 mm


*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M23 PVC Cordsets

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut


Temperature: -25° to +85 °C

Environmental Rating: IP67 and IP68





19-Pin (Voltage: 150 V DC/AC, Current: 8 A (18 gauge), 2A (22 gauge))



	Length	Straight	Pinout
19-Pin Male QD to Flying Leads	1 m	BC-M23M19-1822-1	 <p>Male</p> <ul style="list-style-type: none"> 1 = Purple 2 = Red 3 = Gray 4 = Red/Blue 5 = Green 6 = Blue (18 AWG) 7 = Gray/Pink 8 = White/Green 9 = White/Yellow 10 = White/Gray 11 = Black 12 = Green/Yellow (18 AWG) 13 = Yellow/Brown 14 = Brown/Green 15 = White 16 = Yellow 17 = Pink 18 = Gray/Brown 19 = Brown (18 AWG) <p>18 and 22 AWG Cable ø – 9.8 mm</p>
	2 m	BC-M23M19-1822-2	
	5 m	BC-M23M19-1822-5	
	10 m	BC-M23M19-1822-10	
	15 m	BC-M23M19-1822-10	
	20 m	BC-M23M19-1822-20	



	Length	Straight/Straight (Female/Male)	Pinout
19-Pin Double-Ended	1 m	BC-M23F19-M23M19-1822-1	 <p>Female</p>  <p>Male</p> <ul style="list-style-type: none"> 1 = Purple 2 = Red 3 = Gray 4 = Red/Blue 5 = Green 6 = Blue (18 AWG) 7 = Gray/Pink 8 = White/Green 9 = White/Yellow 10 = White/Gray 11 = Black 12 = Green/Yellow (18 AWG) 13 = Yellow/Brown 14 = Brown/Green 15 = White 16 = Yellow 17 = Pink 18 = Gray/Brown 19 = Brown (18 AWG) <p>18 and 22 AWG Cable ø – 9.8 mm</p>
	2 m	BC-M23F19-M23M19-1822-2	
	5 m	BC-M23F19-M23M19-1822-5	
	10 m	BC-M23F19-M23M19-1822-10	
	15 m	BC-M23F19-M23M19-1822-15	
	20 m	BC-M23F19-M23M19-1822-20	


*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M23 PVC Cordsets

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Temperature: -25° to +85 °C

Environmental Rating: IP67 and IP68



12-Pin (Voltage: 300 V DC/AC, Current: 4 A)



	Length	Straight	Right-Angle		Pinout	
12-Pin Female QD to Flying Leads	1 m	BC-M23F12-22-1	—	<p>Female</p>	1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink 7 = Blue 8 = Red 9 = Orange 10 = Tyrian Purple 11 = Black 12 = Violet	
	2 m	BC-M23F12-22-2	BC-M23F12A-22-2		22 AWG	Cable ø – 6 mm
	5 m	BC-M23F12-22-5	BC-M23F12A-22-5			
	10 m	BC-M23F12-22-10	BC-M23F12A-22-10			
	15 m	BC-M23F12-22-15	—			
	20 m	BC-M23F12-22-20	—			



12-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	BC-M23F12-22-2-SFP	BC-M23F12A-22-2-SFP	<p>Female</p>	1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink 7 = Blue 8 = Red 9 = Orange 10 = Tyrian Purple 11 = Black Cut = Violet 12 = Drain + Braid	
	5 m	BC-M23F12-22-5-SFP	BC-M23F12A-22-5-SFP		22 AWG	Cable ø – 6 mm
	10 m	BC-M23F12-22-10-SFP	BC-M23F12A-22-10-SFP			



12-Pin Male QD to Flying Leads	1 m	BC-M23M12-22-1	—	<p>Male</p>	1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink 7 = Blue 8 = Red 9 = Orange 10 = Tyrian Purple 11 = Black 12 = Violet	
	2 m	BC-M23M12-22-2	—		22 AWG	Cable ø – 9.8 mm
	5 m	BC-M23M12-22-5	—			
	10 m	BC-M23M12-22-10	—			
	15 m	BC-M23M12-22-15	—			
	20 m	BC-M23M12-22-20	—			


*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M23 PVC Cordsets

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Temperature: -25° to +85 °C

Environmental Rating: IP67 and IP68



12-Pin (Voltage: 300 V DC/AC, Current: 4 A)



	Length	Straight/Straight (Female/Male)	Pinout
12-Pin Double-Ended	2 m	BC-M23F12-M23M12-22-2	<p>Female</p> <p>1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink 7 = Blue 8 = Red 9 = Orange 10 = Tyrian Purple 11 = Black 12 = Violet</p> <p>Male</p> <p>22 AWG Cable ø – 6 mm</p>
	5 m	BC-M23F12-M23M12-22-5	
	10 m	BC-M23F12-M23M12-22-10	
	15 m	BC-M23F12-M23M12-22-15	
	20 m	BC-M23F12-M23M12-22-20	


*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M8 PVC Cordsets








Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Temperature: -40° to +70 °C

Environmental Rating: IP67



3-Pin (Voltage: 30 V DC, Current: 4 A)

	Length	Straight	Pinout
 3-Pin Female QD to Flying Leads	0.5 m	BC-M8F3-24-0.5	 Female 1 = Brown 3 = Blue 4 = Black
	1 m	BC-M8F3-24-1	
	2 m	BC-M8F3-24-2	
	5 m	BC-M8F3-24-5	
	8 m	BC-M8F3-24-8	
	10 m	BC-M8F3-24-10	
 3-Pin Male QD to Flying Leads	0.5 m	BC-M8M3-24-0.5	 Male 1 = Brown 3 = Blue 4 = Black
	1 m	BC-M8M3-24-1	
	2 m	BC-M8M3-24-2	
	5 m	BC-M8M3-24-5	
	8 m	BC-M8M3-24-8	
	10 m	BC-M8M3-24-10	
 3-Pin Double-Ended	0.5 m	BC-M8F3-M8M3-24-0.5	 Female 1 = Brown 3 = Blue 4 = Black  Male 1 = Brown 3 = Blue 4 = Black
	1 m	BC-M8F3-M8M3-24-1	
	2 m	BC-M8F3-M8M3-24-2	
	5 m	BC-M8F3-M8M3-24-5	
	8 m	BC-M8F3-M8M3-24-8	
	10 m	BC-M8F3-M8M3-24-10	

*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M8 PVC Cordsets



4-Pin (Voltage: 30 V DC, Current: 4 A)



	Length	Straight	Pinout	
4-Pin Female QD to Flying Leads	0.5 m	BC-M8F4-24-0.5		1 = Brown 2 = White 3 = Blue 4 = Black
	1 m	BC-M8F4-24-1		
	2 m	BC-M8F4-24-2		
	5 m	BC-M8F4-24-5		
	8 m	BC-M8F4-24-8		
	10 m	BC-M8F4-24-10		



4-Pin Male QD to Flying Leads	0.5 m	BC-M8M4-24-0.5		1 = Brown 2 = White 3 = Blue 4 = Black
	1 m	BC-M8M4-24-1		
	2 m	BC-M8M4-24-2		
	5 m	BC-M8M4-24-5		
	8 m	BC-M8M4-24-8		
	10 m	BC-M8M4-24-10		




	Length	Straight/Straight (Female/Male)	Pinout	
4-Pin Double-Ended	0.5 m	BC-M8F4-M8M4-24-0.5		1 = Brown 2 = White 3 = Blue 4 = Black
	1 m	BC-M8F4-M8M4-24-1		
	2 m	BC-M8F4-M8M4-24-2		
	5 m	BC-M8F4-M8M4-24-5		
	8 m	BC-M8F4-M8M4-24-8		
	10 m	BC-M8F4-M8M4-24-10		

*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M8 Field Wireable Connectors

Temperature: -25° to +90 °C

Environmental Rating: IP67



3-Pin (Voltage: 30 V DC/AC, Current: 4 A)



	Straight	Right-Angle	Pinout
3-Pin Female Insulation Displacement	FIC-M8F3	FIC-M8F3A	<p>Female</p>
3-Pin Male Insulation Displacement	FIC-M8F3A	FIC-M8M3A	
3-Pin Female Screw Terminal	FIC-M8F4	FIC-M8F4A	<p>Male</p>
3-Pin Male Screw Terminal	FIC-M8M4	FIC-M8M4A	
			1 = Brown 3 = Blue 4 = Black
			22 AWG

4-Pin (Voltage: 30 V DC/AC, Current: 4 A)




	Straight	Right-Angle	Pinout
4-Pin Female Insulation Displacement	FIC-M8F4	FIC-M8F4A	<p>Female</p>
4-Pin Male Insulation Displacement	FIC-M8M4	FIC-M8M4A	
4-Pin Female Screw Terminal	BFW-M8F4-4X	BFW-M8F4A-4X	<p>Male</p>
4-Pin Male Screw Terminal	BFW-M8M4-4X	BFW-M8M4A-4X	
			1 = Brown 2 = White 3 = Blue 4 = Black
			22 AWG

M12 Field Wireable Connectors

Temperature: -40° to +85 °C

Environmental Rating: IP68



4-Pin (Voltage: 60 V DC/AC, Current: 4 A)



	Straight	Right-Angle	Pinout
4-Pin Female Screw Terminal	BFW-M12F4-6X	BFW-M12F4A-6X	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black</p>
4-Pin Male Screw Terminal	BFW-M12M4-6X	BFW-M12M4A-6X	<p>Male</p> <p>22 AWG</p>

5-Pin (Voltage: 60 V DC/AC, Current: 4 A)



	Straight	Right-Angle	Pinout
5-Pin Female Screw Terminal	BFW-M12F5-6X	BFW-M12F5A-6X	<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p>
5-Pin Male Screw Terminal	BFW-M12M5-6X	BFW-M12M5A-6X	<p>Male</p> <p>22 AWG</p>

8-Pin (Voltage: 30 V DC/AC, Current: 2 A)




	Straight	Right-Angle	Pinout
8-Pin Female Screw Terminal	BFW-M12F8-8X	BFW-M12F8A-8X	<p>Female</p> <p>1 = Brown 2 = Or/Bk 3 = Orange 4 = White 5 = Black 6 = Blue 7 = Gr/Ye 8 = Violet</p>
8-Pin Male Screw Terminal	BFW-M12M8-8X	BFW-M12M8A-8X	<p>Male</p> <p>22 AWG</p>





M12 Field Wireable Slide Lock

Temperature: -40° to +85 °C





Environmental Rating: IP68



4-Pin (Voltage: 60 V DC/AC, Current: 4 A)

	Straight	Right-Angle	Pinout
 4-Pin Female Slide Lock Terminal	BFW-M12F4-6SL	BFW-M12F4A-6SL	Female  1 = Brown 2 = White 3 = Blue 4 = Black
 4-Pin Male Slide Lock Terminal	BFW-M12M4-6SL	BFW-M12M4A-6SL	Male  1 = Brown 2 = White 3 = Blue 4 = Black 22 AWG

5-Pin (Voltage: 60 V DC/AC, Current: 4 A)

	Straight	Right-Angle	Pinout
 5-Pin Female Slide Lock Terminal	BFW-M12F5-6SL	BFW-M12F5A-6SL	Female  1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
 5-Pin Male Slide Lock Terminal	BFW-M12M5-6SL	BFW-M12M5A-6SL	Male  1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray 22 AWG

Smarter Automation. Better Solutions.™

Banner Engineering designs and manufactures industrial automation products including sensors, smart IIoT and industrial wireless technologies, LED lights and indicators, measurement devices, machine safety equipment, as well as barcode scanners and machine vision. These solutions help make many of the things we use every day, from food and medicine to cars and electronics. A high-quality, reliable Banner product is installed somewhere around the world every two seconds. Headquartered in Minneapolis since 1966, Banner is an industry leader with more than 10,000 products, operations on five continents, and a world-wide team of more than 5,500 employees and partners. Our dedication to innovation and personable service makes Banner a trusted source of smart automation technologies to customers around the globe.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Banner Engineering:](#)

[CSA-M1241M1241](#) [CSB-M1250M1250-T](#) [CSB-M1251FM1251M](#) [CSB-M1251M1251B](#) [CSRB-M1240M1241](#) [CSRB-M1240M1242](#) [CSA-M1240M1246](#) [CSA-M1243M1243](#) [CSA-M1246M1246](#) [CSRB-M1240M1243](#) [CSRB-M1240M1244](#) [CSB4-M1251M1250](#) [CSB-M1250M1250A](#) [CSA-M1240M1241](#) [CSA-M1240M1243](#) [MQDC-1210](#) [MQDC-1215](#) [MQDC-1230](#) [MQDC-1206](#)