

SPECIFICATION SHEET

CONTACTOR CONTROL MODULE

PAGE
1 of 1



DIVERSIFIED ELECTRONICS
8019 Ohio River Blvd.
Newell, WV 26050
Phone: (800) 727-5646

CUSTOMER

GENERAL ELECTRIC MEBANE, NC

ISSUED

5-13-96

CUSTOMER PART NO.

DEI PART NO.

SP-0310

INPUT VOLTAGE: 120 VAC, Nominal
50 VAC min., 132 VAC max.

OUTPUT VOLTAGE
Initial: 100-110 VDC for 1 Second(Unfiltered)
Continuous: 20 VDC after 1 Second(Unfiltered)

OUTPUT CURRENT
Initial: 6 Amps for 1 Second
Continuous: 1.5 Amps

TIME DELAY: 1 Second \pm 5%(during which full voltage is applied to the contactor coil.)

TEMPERATURES
Operate: 0°C to +55°C
Storage: -45°C to +85°C



ENCLOSURE: Style "N" Epoxy Encapsulated

TERMINATION: (4) #8-32 Screw Terminals

OPERATION: Upon application of the input voltage to the unit, a 1 second delay begins, during which a nominal 110 VDC is produced on the output. After the 1 second delay, the triggering of the internal SCRs is delayed to produce a nominal 20 VDC output.



REV.	DATE	E.C.O.	APP.
A	3-27-97	97-49	G.S.
B	5-7-97	97-72	G.S.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ATC Diversified Electronics:](#)

[SP0310](#)