


Data sheet

chainflex® CF890



Control cable (Class 3.1.3.1) • For flexing applications • iguPUR outer jacket • Oil-resistant
• Flame retardant



1. Outer jacket: Pressure extruded iguPUR mixture
2. Core insulation: Mechanically high-quality TPE mixture
3. Conductor: Stranded conductor consisting of bare copper wires
4. Filling: Plastic yarns

Example image

For detailed overview please see design table

Cable structure

	Conductor	Conductor consisting of bare copper wires (according to DIN EN 60228).
	Core insulation	Mechanically high-quality TPE mixture.
	Core structure	Cores wound with an optimised pitch length.
	Core identification	Black cores with white numbers, one green-yellow core.
	Outer jacket	Low-adhesion iguPUR mixture, adapted to suit the requirements in e-chains®. Colour: Jet black (similar to RAL 9005) Printing: white

„00000 m*** igus chainflex M CF890.--.---① ---② 300/500V E310776

cRUus AWM Style 20940 VW-1 AWM I/II A/B 80°C 600V FT1 EAC CE UKCA

RoHS-II conform www.igus.de +++ chainflex cable works +++

* Length printing: Not calibrated. Only intended as an orientation aid.

① / ② Cable identification according to Part No. (see technical table).

Example: ... chainflex CF890.15.04 4G1.5 300 V/500 V ...



Example image

Data sheet

chainflex® CF890



Control cable (Class 3.1.3.1) • For flexing applications • iguPUR outer jacket • Oil-resistant
• Flame retardant



Dynamic information

	Bend radius	e-chain® linear flexible fixed	minimum 12.5 x d minimum 10 x d minimum 7 x d
	Temperature	e-chain® linear flexible fixed	-20 °C up to +80 °C -40 °C up to +80 °C (following DIN EN 60811-504) -50 °C up to +80 °C (following DIN EN 50305)
	v max.	unsupported	3 m/s
	a max.		20 m/s ²
	Travel distance		Unsupported travel distances up to 10 m, Class 1

These values are based on specific applications or tests. They do not represent the limit of what is technically feasible.

Guaranteed service life according to guarantee conditions

Double strokes	1 million	3 million	5 million
Temperature, from/to [°C]	R min. [x d]	R min. [x d]	R min. [x d]
-20/-10	15	16	17
-10/+70	12.5	13.5	14.5
+70/+80	15	16	17

Minimum guaranteed service life of the cable under the specified conditions.
The installation of the cable is recommended within the middle temperature range.

Electrical information

	Nominal voltage	300/500 V 600 V (following UL)
	Testing voltage	2000 V (following DIN EN 50395)



Example image

Data sheet

chainflex® CF890



Control cable (Class 3.1.3.1) • For flexing applications • iguPUR outer jacket • Oil-resistant
• Flame retardant



Properties and approvals

	UV resistance	Medium
	Oil resistance	Oil-resistant (following DIN EN 50363-10-2), Class 3
	Flame retardant	According to IEC 60332-1-2, Cable Flame, VW-1, FT1, FT2 / Horizontal Flame
	Silicone-free	Free from silicone which can affect paint adhesion (following PV 3.10.7 – status 1992)
	PFAS-free	Use of PFAS-free materials according to the content of the REACH directive and its rules for the production and processing of chemical substances
	UL verified	Certificate No. V293560: „igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year“
	UL/CSA AWM	Details see table UL/CSA AWM
	REACH	In accordance with regulation (EC) No. 1907/2006 (REACH)
	Lead-free	Following 2011/65/EC (RoHS-II/RoHS-III)
	CE	Following 2014/35/EU



igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



Properties and approvals

UL/CSA AWM Details

Conductor nominal cross section [mm²]	Number of cores	UL style core insulation	UL style outer jacket	UL Voltage Rating [V]	UL Temperature Rating [°C]
0.5	2-25	11323	20940	600	80
0.75	2-25	11323	20940	600	80
1	2-25	11323	20940	600	80
1.5	2-25	11323	20940	600	80
2.5	3-25	11323	20940	600	80

Example image

igus® chainflex® CF890

Data sheet

chainflex® CF890




Control cable (Class 3.1.3.1) ● For flexing applications ● iguPUR outer jacket ● Oil-resistant
● Flame retardant



Example image

Typical lab test setup for this cable series

Test bend radius R	approx. 75 - 225 mm
Test travel S	approx. 1 - 15 m
Test duration	minimum 2 - 4 million double strokes
Test speed	approx. 0.5 - 2 m / s
Test acceleration	approx. 0.5 - 1.5 m / s ²



Typical application areas

- For flexing applications, Class 3
- Especially for unsupported travels, Class 1
- With influence of oil, Class 3
- No torsion, Class 1
- Indoor and outdoor applications without direct solar radiation
- Machining units/machine tools, low temperature applications



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Data sheet

chainflex® CF890



Control cable (Class 3.1.3.1) • For flexing applications • iguPUR outer jacket • Oil-resistant
• Flame retardant

Technical tables:

Mechanical information

Part No.	Number of cores and conductor nominal cross section [mm²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF890.05.02	2x0.5	5.0	11	30
CF890.05.03	3G0.5	5.5	16	34
CF890.05.04	4G0.5	6.0	21	44
CF890.05.05	5G0.5	6.5	26	53
CF890.05.07	7G0.5	7.5	37	70
CF890.05.12	12G0.5	8.5	63	105
CF890.05.18	18G0.5	10.0	94	155
CF890.05.25	25G0.5	12.0	128	222
CF890.07.02	2x0.75	5.5	16	38
CF890.07.03	3G0.75	6.0	24	46
CF890.07.04	4G0.75	6.5	32	58
CF890.07.05	5G0.75	7.0	40	71
CF890.07.07	7G0.75	8.0	56	96
CF890.07.12	12G0.75	10.0	94	146
CF890.07.18	18G0.75	11.5	140	162
CF890.07.25	25G0.75	13.5	194	278
CF890.10.02	2x1.0	6.0	21	46
CF890.10.03	3G1.0	6.5	32	56
CF890.10.04	4G1.0	7.0	42	58
CF890.10.05	5G1.0	7.5	52	89
CF890.10.07	7G1.0	8.5	73	117
CF890.10.12	12G1.0	10.5	124	178
CF890.10.18	18G1.0	12.5	186	273
CF890.10.25	25G1.0	15.0	258	375
CF890.15.02	2x1.5	6.5	32	62
CF890.15.03	3G1.5	7.0	47	76
CF890.15.04	4G1.5	7.5	63	97
CF890.15.05	5G1.5	8.5	78	117
CF890.15.07	7G1.5	10.0	109	163
CF890.15.12	12G1.5	12.0	186	256
CF890.15.18	18G1.5	14.5	279	362
CF890.15.25	25G1.5	17.5	387	502

Note: The given outer diameters are maximum values and may tend toward lower tolerance limits.

G = with green-yellow earth core x = without earth core



igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



Example image

Data sheet

chainflex® CF890



Control cable (Class 3.1.3.1) • For flexing applications • iguPUR outer jacket • Oil-resistant
• Flame retardant

Technical tables:

Mechanical information

Part No.	Number of cores and conductor nominal cross section [mm²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF890.25.03	3G2.5	8.5	78	136
CF890.25.04	4G2.5	9.0	103	145
CF890.25.05	5G2.5	10.0	129	175
CF890.25.07	7G2.5	12.0	181	246
CF890.25.12	12G2.5	15.0	327	408
CF890.25.25	25G2.5	21.5	638	786

Note: The given outer diameters are maximum values and may tend toward lower tolerance limits.
G = with green-yellow earth core x = without earth core

Electrical information

Conductor nominal cross section [mm²]	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2) [Ω/km]	Max. current rating at 30 °C [A]
0.5	39	10
0.75	26	14
1	19.5	17
1.5	13.3	21
2.5	8	30

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.



igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



Example image

igus® chainflex® CF890

Data sheet

chainflex® CF890



Control cable (Class 3.1.3.1) • For flexing applications • iguPUR outer jacket • Oil-resistant
• Flame retardant

Design table

Part No.	Number of cores	Core design	Part No.	Number of cores	Core design
CF890.XX.02	2		CF890.XX.07	7	
CF890.XX.03	3		CF890.XX.12	12	
CF890.XX.04	4		CF890.XX.18	18	
CF890.XX.05	5		CF890.XX.25	25	



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[igus:](#)

<u>CF890.15.02</u>	<u>CF890.15.04</u>	<u>CF890.15.03</u>	<u>CF890.05.05</u>	<u>CF890.15.18</u>	<u>CF890.25.07</u>	<u>CF890.25.25</u>	<u>CF890.10.02</u>
<u>CF890.05.04</u>	<u>CF890.07.12</u>	<u>CF890.10.07</u>	<u>CF890.05.18</u>	<u>CF890.10.03</u>	<u>CF890.07.18</u>	<u>CF890.25.03</u>	<u>CF890.07.02</u>
<u>CF890.10.25</u>	<u>CF890.05.12</u>	<u>CF890.15.07</u>	<u>CF890.15.05</u>	<u>CF890.05.02</u>	<u>CF890.10.04</u>	<u>CF890.05.03</u>	<u>CF890.07.25</u>
<u>CF890.25.04</u>	<u>CF890.10.05</u>	<u>CF890.10.18</u>	<u>CF890.15.12</u>	<u>CF890.25.12</u>	<u>CF890.07.04</u>	<u>CF890.07.07</u>	<u>CF890.10.12</u>
<u>CF890.05.07</u>	<u>CF890.07.05</u>	<u>CF890.15.25</u>	<u>CF890.25.05</u>	<u>CF890.05.25</u>	<u>CF890.07.03</u>		