


Captive Screw Type 1 6-32 Thread



Create a part number:

Length	Material	Finish
FCXXXX	XX	XX

Captive Screws - 6-32 Thread						
✓	FCXXXX	Length (L)	H.D. +.015 -.000	S.L. +.010 -.010	D. +.010 -.000	Knurl TPI
	FC0105	21/32	5/16	3/8	1/16	35
	FC0106	23/32	5/16	7/16	1/16	35
	FC0107	25/32	5/16	1/2	1/16	35
	FC0108	27/32	5/16	9/16	1/16	35
	FC0109	29/32	5/16	5/8	1/16	35
	FC0110	21/32	3/8	3/8	1/16	30
	FC0111	23/32	3/8	7/16	1/16	30
	FC0112	25/32	3/8	1/2	1/16	30
	FC0113	27/32	3/8	9/16	1/16	30
	FC0114	29/32	3/8	5/8	1/16	30

Material	
✓	Material Code (XX)
B	Brass
S	Steel
SS	Stainless Steel

✓	Compatible Finish (XX)	
	B, S, SS	0 - Plain
	B, S	5 - Nickel Plate (QQ-N-290)
	B, S	12 - Zinc Clear (ASTM-B-633)
	B, S	16 - Electro Tin (MIL-T-10727 TYPE 1)
	SS	20 - Passivation (MIL-F-14072D)
	B, S, SS	26 - Black Oxide
	B, S	28 - Zinc Yellow (ASTM-B-633)

Tolerances
Unless otherwise Specified
 .xxx +/- .005
 .xx +/- .010
 Angular +/- 1 Degree
 Linear +/- .005
Break all sharp edges

Source Control Drawing:
 To be produced by
 Fascomp Electronic Hardware



This document is the property of Fascomp Inc. and shall not be reproduced, distributed, or used as a basis for manufacturing without written permission from Fascomp Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fascomp:

[FC0105-SS](#) [FC0106-SS](#) [FC0107-SS](#) [FC0108-SS](#) [FC0109-SS](#) [FC0110-SS](#) [FC0111-SS](#) [FC0112-SS](#) [FC0113-SS](#)
[FC0114-SS](#)