


Captive Screw Type 2 4-40 Thread



Create a part number:

Length	Material	Finish
FCXXXX	XX	XX
_____ - _____ - _____		

Captive Screws - 4-40 Thread

FCXXXX	Length (L)	H.D. +.015 -.000	H.L. +.010 -.010	S.L. +.010 -.010	D. +.010 -.000
FC0367	3/8	1/4	1/4	11/64	.078
FC0368	7/16	1/4	1/4	15/64	.078
FC0369	1/2	1/4	1/4	19/64	.078
FC0370	9/16	1/4	1/4	23/64	.078
FC0371	5/8	1/4	1/4	27/64	.078
FC0372	11/16	1/4	1/4	31/64	.078
FC0373	3/4	1/4	1/4	35/64	.078
FC0374	13/16	1/4	1/4	39/64	.078
FC0375	7/8	1/4	1/4	43/64	.078
FC0376	15/16	1/4	1/4	47/64	.078
FC0377	1	1/4	1/4	51/64	.078
FC0378	3/8	5/16	5/16	11/64	.078
FC0379	7/16	5/16	5/16	15/64	.078
FC0380	1/2	5/16	5/16	19/64	.078
FC0381	9/16	5/16	5/16	23/64	.078
FC0382	5/8	5/16	5/16	27/64	.078
FC0383	11/16	5/16	5/16	31/64	.078
FC0384	3/4	5/16	5/16	35/64	.078
FC0385	13/16	5/16	5/16	39/64	.078
FC0386	7/8	5/16	5/16	43/64	.078
FC0387	15/16	5/16	5/16	47/64	.078
FC0388	1	5/16	5/16	51/64	.078

Material

Material Code (XX)
B Brass
S Steel
SS Stainless Steel

Compatible Finish (XX)

B, S, SS	0 - Plain
B, S	5 - Nickel Plate (QQ-N-290)
B, S	12 - Zinc Clear (ASTM-B-633)
B, S	16 - Electro Tin (MIL-T-10727 TYPE 1)
SS	20 - Passivation (MIL-F-14072D)
B, S, SS	26 - Black Oxide
B, S	28 - Zinc Yellow (ASTM-B-633)

Tolerances
Unless otherwise Specified
 .xxx +/- .005
 .xx +/- .010
 Angular +/- 1 Degree
 Linear +/- .005
Break all sharp edges

Source Control Drawing:
 To be produced by
 Fascomp Electronic Hardware



This document is the property of Fascomp Inc. and shall not be reproduced, distributed, or used as a basis for manufacturing without written permission from Fascomp Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fascomp:

[FC0367-SS](#) [FC0368-SS](#) [FC0369-SS](#) [FC0370-SS](#) [FC0371-SS](#) [FC0373-SS](#) [FC0375-SS](#) [FC0377-SS](#) [FC0378-SS](#)
[FC0379-SS](#) [FC0380-SS](#) [FC0381-SS](#) [FC0382-SS](#) [FC0384-SS](#) [FC0386-SS](#) [FC0388-SS](#)