


Captive Screw Type 6 6-32 Thread



Create a part number:

Length	Material	Finish
FCXXXX	XX	XX

Captive Screws - 6-32 Thread				
✓ FCXXXX	Length (L)	H.D. +.005 - .005	S.L. +.005 - .000	
FC7085	17/32	9/32	5/16	
FC7086	19/32	9/32	3/8	
FC7087	21/32	9/32	7/16	

Material		
✓ Material Code (XX)		
B	Brass	
S	Steel	
SS	Stainless Steel	

✓ Compatible Finish (XX)		
B, S, SS	0 - Plain	
B, S	5 - Nickel Plate (QQ-N-290)	
B, S	12 - Zinc Clear (ASTM-B-633)	
B, S	16 - Electro Tin (MIL-T-10727 TYPE 1)	
SS	20 - Passivation (MIL-F-14072D)	
B, S, SS	26 - Black Oxide	
B, S	28 - Zinc Yellow (ASTM-B-633)	

Tolerances
Unless otherwise Specified
 .xxx +/- .005
 .xx +/- .010
 Angular +/- 1 Degree
 Linear +/- .005
Break all sharp edges



Source Control Drawing:
 To be produced by
 Fascomp Electronic Hardware

This document is the property of Fascomp Inc. and shall not be reproduced, distributed, or used as a basis for manufacturing without written permission from Fascomp Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fascomp:

[FC7085-SS](#) [FC7086-SS](#) [FC7087-SS](#)