



## Part Number: D3C1727



### Electrical Specifications

|                        |           |
|------------------------|-----------|
| Frequency Range (GHz): | 1.7 – 2.7 |
| Isolation (dB):        | 20 MIN    |
| Insertion Loss (dB):   | 0.5 MAX   |
| VSWR:                  | 1.3:1 MIN |
| Forward Power (W):     | 30 AVG    |
|                        | 50 PK     |


### Mechanical/Environmental Specifications

|                   |                            |
|-------------------|----------------------------|
| Connector Type:   | SMA                        |
| Connector Body:   | Passivated stainless steel |
| Connector Pin:    | Gold plated copper         |
| Load Body:        | Brass                      |
| Magnetic Shunt:   | Nickel plated CRS          |
| Operational Temp: | 0°C to +70°C               |
| Weight (oz)       | 6.0 MAX                    |

### D3C1727 Dimensions



### D3C1727-3 Dimensions




| Type of Device                                                              | PN Suffix | Connector Configuration<br>Input / Output | PN Example |
|-----------------------------------------------------------------------------|-----------|-------------------------------------------|------------|
| Single Junction Circulator<br>3-Port Device<br><br>Port 1 / Port 2 / Port 3 | No Dash   | Female / Female / Female                  | D3C1727    |
|                                                                             | -1        | Male / Female / Female                    | D3C1727-1  |
|                                                                             | -2        | Female / Male / Female                    | D3C1727-2  |
|                                                                             | -3        | Male / Male / Male                        | D3C1727-3  |
|                                                                             | -4        | Female / Female / Male                    | D3C1727-4  |
|                                                                             | -5        | Male / Female / Male                      | D3C1727-5  |
|                                                                             | -6        | Male / Male / Female                      | D3C1727-6  |
|                                                                             | -7        | Female / Male / Male                      | D3C1727-7  |



## MEASURED DATA

Part Number: D3C1727, P1→P2, P3 Terminated with 50Ω, +25°C



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DiTom:](#)

[D3C1727](#) [D3C1727-1](#) [D3C1727-2](#) [D3C1727-3](#) [D3C1727-4](#) [D3C1727-5](#) [D3C1727-6](#) [D3C1727-7](#)