

Single Phase Glass Passivated Silicon Bridge Rectifier

$V_{RRM} = 50 \text{ V} - 400 \text{ V}$

$I_O = 2 \text{ A}$

Features

- Ideal for printed circuit board
- Plastic material has Underwriters Laboratory Flammability Classification 94V-0
- Built-in printed circuit board stand-offs
- High temperature soldering guaranteed 265°C/ 10 seconds
- High case dielectric strength
- Types from 50 V to 400 V V_{RRM}
- Not ESD Sensitive

Mechanical Data



Case: Reliable low cost construction

Terminals: Plated leads, solderable per MIL-STD-202, Method 208

Mounting position: Any

Weight: 0.065 oz, 2.2 grams

KBP Package



Maximum ratings at $T_j = 25^\circ\text{C}$, unless otherwise specified

Parameter	Symbol	Conditions	KBP2005G	KBP201G	KBP202G	KBP204G	Unit
Repetitive peak reverse voltage	V_{RRM}		50	100	200	400	V
RMS reverse voltage	V_{RMS}		35	70	140	280	V
DC blocking voltage	V_{DC}		50	100	200	400	V
Operating temperature	T_j		-55 to 150	-55 to 150	-55 to 150	-55 to 150	$^\circ\text{C}$
Storage temperature	T_{stg}		-55 to 150	-55 to 150	-55 to 150	-55 to 150	$^\circ\text{C}$

Electrical characteristics at $T_j = 25^\circ\text{C}$, unless otherwise specified

Single phase, half sine wave, 60 Hz, resistive or inductive load

For capacitive load derate current by 20%

Parameter	Symbol	Conditions	KBP2005G	KBP201G	KBP202G	KBP204G	Unit
Maximum average forward rectified current	I_O	$T_a = 50^\circ\text{C}$	2	2	2	2	A
Peak forward surge current	I_{FSM}	single sine-wave	60	60	60	60	A
Maximum instantaneous forward voltage per leg	V_F	$I_F = 2 \text{ A}$	1.1	1.1	1.1	1.1	V
Maximum reverse current at rated DC blocking voltage per leg	I_R	$T_a = 25^\circ\text{C}$	10	10	10	10	μA
		$T_a = 100^\circ\text{C}$	500	500	500	500	

Thermal characteristics

Thermal resistance	$R_{\theta JL}$		25	25	25	25	$^\circ\text{C/W}$
--------------------	-----------------	--	----	----	----	----	--------------------

FIG.1-MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.2-MAXIMUM NON-RECURRENTIVE FORWARD SURGE CURRENT




FIG.3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS PER BRIDGE ELEMENT






FIG.4-TYPICAL REVERSE CHARACTERISTICS PER BRIDGE ELEMENT




Package dimensions and terminal configuration

Product is marked with part number and terminal configuration.



Dimensions in inches and (millimeters)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Navitas Semiconductor:](#)

[KBP202G](#)