



Part Number: D4C4080YMG


Electrical Specifications

Frequency Range (GHz):	4.0 – 8.0
Isolation (dB):	16 MIN (per junction)
Insertion Loss (dB):	0.4 MAX (per junction)
Return Loss (dB):	16 MIN (per junction)
Forward Power (W):	20 AVG
	30 PK

Mechanical/Environmental Specifications

Connector Type:	SMA
Connector Body:	Passivated stainless steel
Connector Pin:	Gold plated copper
Load Body:	Brass
Magnetic Shunt:	Nickel plated CRS
Magnetically Shielded:	Yes
Operational Temp:	< 77K
Weight (oz)	4.0 MAX

D4C4080YMG-2 Dimensions




Type of Device	PN Suffix	Connector Configuration Input / Output	PN Example
Dual Junction Circulator 4-Port Device Port 1 / Port 2 / Port 3 / Port 4	No Dash	Female / Female / Female / Female	D4C4080YMG
	-1	Male / Female / Female / Female	D4C4080YMG-1
	-2	Female / Male / Female / Female	D4C4080YMG-2
	-3	Male / Male / Male / Male	D4C4080YMG-3
	-4	Female / Female / Male / Female	D4C4080YMG-4
	-5	Female / Female / Female / Male	D4C4080YMG-5



MEASURED DATA

Part Number: D4C4080YMC, P1→P2, P3 & P4 Terminated with 50Ω, Measured at 77K



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DiTom:](#)

[D4C4080YMG](#) [D4C4080YMG-1](#) [D4C4080YMG-2](#) [D4C4080YMG-3](#) [D4C4080YMG-4](#) [D4C4080YMG-5](#)