

## Silicon Power Schottky Diode


$V_{RRM} = 150\text{ V} - 200\text{ V}$

$I_{F(AV)} = 120\text{ A}$

### Features

- High Surge Capability
- Types from 150 V to 200 V  $V_{RRM}$
- Isolation Type Package
- Electrically Isolated Base Plate
- Not ESD Sensitive

### Three Tower Package



Maximum ratings, at  $T_j = 25\text{ °C}$ , unless otherwise specified ("R" devices have leads reversed)

| Parameter                       | Symbol    | Conditions | MBRT120150(R) | MBRT120200(R) | Unit |
|---------------------------------|-----------|------------|---------------|---------------|------|
| Repetitive peak reverse voltage | $V_{RRM}$ |            | 150           | 200           | V    |
| RMS reverse voltage             | $V_{RMS}$ |            | 106           | 141           | V    |
| DC blocking voltage             | $V_{DC}$  |            | 150           | 200           | V    |
| Operating temperature           | $T_j$     |            | -55 to 150    | -55 to 150    | °C   |
| Storage temperature             | $T_{stg}$ |            | -55 to 150    | -55 to 150    | °C   |

Electrical characteristics, at  $T_j = 25\text{ °C}$ , unless otherwise specified

| Parameter                                                                    | Symbol      | Conditions                                    | MBRT120150(R) | MBRT120200(R) | Unit |
|------------------------------------------------------------------------------|-------------|-----------------------------------------------|---------------|---------------|------|
| Average forward current (per pkg)                                            | $I_{F(AV)}$ | $T_C = 125\text{ °C}$                         | 120           | 120           | A    |
| Peak forward surge current (per leg)                                         | $I_{FSM}$   | $t_p = 8.3\text{ ms}$ , half sine             | 800           | 800           | A    |
| Maximum instantaneous forward voltage (per leg)                              | $V_F$       | $I_{FM} = 60\text{ A}$ , $T_j = 25\text{ °C}$ | 0.88          | 0.92          | V    |
| Maximum instantaneous reverse current at rated DC blocking voltage (per leg) | $I_R$       | $T_j = 25\text{ °C}$                          | 1             | 1             | mA   |
|                                                                              |             | $T_j = 100\text{ °C}$                         | 10            | 10            |      |
|                                                                              |             | $T_j = 150\text{ °C}$                         | 30            | 30            |      |

### Thermal characteristics

|                                             |                 |      |      |      |
|---------------------------------------------|-----------------|------|------|------|
| Thermal resistance, junction-case (per leg) | $R_{\theta JC}$ | 0.80 | 0.80 | °C/W |
|---------------------------------------------|-----------------|------|------|------|

Figure.1-Typical Forward Characteristics




Figure.2-Forward Derating Curve




Figure.3-Peak Forward Surge Current








Figure.4-Typical Reverse Characteristics



## Package dimensions and terminal configuration

Product is marked with part number and terminal configuration.



| DIM | Inches           |       | Millimeters |       |
|-----|------------------|-------|-------------|-------|
|     | Min              | Max   | Min         | Max   |
| A   | 3.150            | NOM   | 80.01       | NOM   |
| B   | 1.565            | 1.585 | 39.75       | 40.26 |
| C   | 0.700            | 0.800 | 17.78       | 20.32 |
| E   | 0.119            | 0.132 | 3.02        | 3.35  |
| F   | 1.327            | ----- | 33.72       | ----- |
| G   | 3.550            | 3.650 | 90.17       | 92.71 |
| H   | 0.677            | 0.720 | 17.20       | 18.30 |
| J   | 1/4 -20 UNC FULL |       |             |       |
| K   | 0.472            | 0.511 | 12          | 13    |
| M   | 0.275            | 0.295 | 6.99        | 7.49  |
| N   | 2.380            | 2.460 | 60.5        | 62.5  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Navitas Semiconductor:](#)

[MBRT120200](#)