



Catalog No. 9T10A1025

Description: 3A,112.5kVA,480-220Y,150C,N2,K1,DOE

UPC No 783173901847

Home > Transformers > Dry Type Vented > General Purpose

ABB's Low Voltage Dry Type transformers are built to last and are designed with exclusive features. With easy installation and all of the specifications you trust, it's easy to see why ABB QL dry type transformers are preferred by contractors. Our Type QL transformers meet DOE efficiency standards. They are available with aluminum or copper windings and in all three temperature rise ratings.

Descriptors

Category	General Purpose
GO Schedule	L1

Specifications

TransType	DOE 2016
Phase	3
PriVoltage	480
SecVoltage	220Y/127
KVA	112.5 KVA
Coil Material	AL
TempRise	150.0 °C
Frequency	60 Hz
Impedance	4.1 %
AmbTemp	40.0 °C
EnergyEfficiency	DOE 2016
KFactor	K1
Enclosure Type	NEMA 2
Sound	Std

Classifications

UL	Yes
----	-----

Publications

Title	Publication No.	Publication Type
UL Nameplate Drawing	9T10A1025-LBL	Connection Diagram
UL Nameplate Drawing 9T10A1025-LBL		

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABB:](#)

[9T10A1025](#)