

TW5252



TW5252 Smart GNSS Antenna

Overview

The TW5252 is a multi-constellation GNSS Receiver which provides simultaneous GPS/GLONASS + SBAS reception. It is designed for use in professional grade digital tracking/positioning applications.

The TW5252 GNSS Smart Antenna uses a state of the art multi-constellation GNSS receiver which provides 72 high sensitivity tracking channels which can be configured to acquire and track 3 concurrent GNSS constellations (GPS, Galileo, GLONASS and Beidou) plus SBAS (WAAS, EGNOS, MSAS and GAGAN) and QZSS augmentation signals simultaneously. Differential GPS corrections may also be supplied via RTCM formatted corrections messages.


The TW5252 employs Tallysman's Accutenna™ dual feed antenna patch technology which greatly improves rejection of multi-path signal interference, across the whole GNSS band. The addition of pre- and post- filtering within the RF signal chain greatly improves immunity to jamming carriers typical within urban environments.

The TW5252 can be configured to output a variety of NMEA 0183 message lists with navigation update rates up to 5Hz. An RS232 interface is provided for data communication with input voltage range from 5V to 36V suitable for Automotive applications.

Tallysman's Windows™ based Configurator enables simple configuration of parameters such as baud rates, output message rates, constellation, tracking parameters.

Interface

The TW5252 has a 5 meter cable terminated in RJ12 connector. Adaptor cables are available to interface to for a variety of Two-Way radios, PC, etc contact Tallysman for details.



Mechanical Dimensions (mm)

Features

- Multi-Constellation Receiver/Antenna
- Concurrent tracking of 3 constellations
- 72 Channel simultaneous operation
- High performance tracking (-164 dBm)
- WAAS, EGNOS, MSAS & GAGAN + QZSS
- DGPS corrections using RTCM input
- Navigation rates 1 to 5 Hz
- Conditioned ignition input for Tait Radios
- 5V to 36V automotive operation
- Accutenna™ Technology
- Pre- and Post- LNA filtering
- Superior multi-path signal rejection
- Industrial grade IP67 enclosure
- RoHS, Reach, RED compliant, CE Marking

TW5252 Smart GNSS Antenna

Specifications

Antenna		Shock.....Vertical axis 50G,other axis 30G 3 axis sweep – 15 min	
Architecture.....	Dual Feed	Vibration.....10-200 Hz log sweep 3G	
Axial Ratio.....	< 1 dB typical.	Sensitivity	
Frequencies.....	GPS/QZSS L1 C/A, GLONASS L10F BeiDou B1I, Galileo E1B/C	Tracking & Nav	-164 dBm 1
SBAS	WAAS, EGNOS, MSAS, GAGAN	Cold starts	-148 dBm
Channels.....	72-Channel u-blox M8 engine	Hot starts	-157 dBm
Interface		Acquisition	
Pwr, Gnd		Cold start	26 sec
Tx, RX	RS232	Aided 3 sec	
Mechanical		Reacquisition	1 sec
Dimensions	57 mm dia. x 15 mm H	Accuracy	
Weight.....	130 g	Position Accuracy.....	2.5m CEP (Horizontal)
Mounting Method	Magnetic Mount	Velocity Accuracy	0.05 m/s
Cable Length.....	5 m with RJ12 termination	Heading Accuracy	0.3 deg
Enclosure.....	Industrial grade magnetic mount weatherproof IP67	Operational Limits	
Electrical		Dynamics	4 g
Voltages	5 V to 36 VDC	Altitude	50,000 m
Current	<500 mW nominal Operating	Velocity	500 m/s
Environmental		Serial Protocol	
Operating Temperature.....	-40°C to +85°C	Output.....	NMEA 0183
Storage Temperature.....	-45°C to +85°C	Input	RTCM
Weatherproof	IP67	Baud Rate.....	Configurable up to 230400 bps
		Update Rate.....	Configurable up to 5Hz

Ordering Information:

32-5252-7-10-05-ccc

ccc= Custom Configuration (Contact Tallysman for “Custom” details e.g. configuration, radio cable type.

e.g. PC0= NMEA out, no adaptor cable

TC4= Tait NMEA, 27-0118-1 radio cable

TW5252 Configuration Cable

27-0117-0 T

Please refer to the Ordering Guide for the current and complete list of available products.

About Tallysman: With global headquarters and manufacturing in Ottawa, Canada, Tallysman is a leading manufacturer of high-precision antennas and components for Global Navigation Satellite System (GNSS) applications. Tallysman's mission is to support the needs of a new generation of positioning systems by delivering unprecedented antenna precision at competitive prices. Learn more at www.tallysman.com

© 2023 Tallysman Inc. All rights reserved. Tallysman, the “When Precision Matters” tag line and the Tallysman logo are trademarks or registered trademarks of Tallysman Inc. and/or its affiliates in Canada and certain other countries. All other trademarks mentioned in this document are the property of their respective owners. The information presented is subject to change without notice. Tallysman assumes no responsibility for any errors or omissions in this document. Tallysman Wireless Inc. hereby disclaims any or all warranties and liabilities of any kind.

Contact us:
info@tallysman.com
T: +1 613 591-3131

Tallysman Wireless Inc.
36 Steacie Drive,
Ottawa ON
K2K 2A9 Canada

www.tallysman.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Calian:](#)

[33-5252-7-10-05-PCO](#)