

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product or component type	Coded magnetic system
Contacts type and composition	1 NO
Material	Plastic
Electrical connection	Pre-cabled
System Voltage	250 V DC

Complementary

Protection type	Overload and short-circuit protection
Breaking capacity	15 VA

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)

Ordering and shipping details

Category	22487 - SENSORS, PROXIMITY, U S
Discount Schedule	DS2
GTIN	00785901091981
Nbr. of units in pkg.	1
Package weight(Lbs)	0.28000000000000003
Returnability	N
Country of origin	US

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[SGA8040](#)