


OAT615 Fan Tray



Universal Input 90 -264VAC
482.6mm x 44.5mm x 83.8mm
(19" x 1.75" x 3.3")



Switching AC/DC Adaptor	12V	<u>Operating Temperature</u> -10°C ~ +50°C, 20 - 90% RH
DC Output Power	60 W (Max Load 5A)	<u>Storage Temperature</u> -40°C ~ +85°C, 10 - 95% RH

Description	<ul style="list-style-type: none"> • Supplied with included Universal 90-264VAC Input external power supply • 1U High, Rack mount configuration • Cord options of either IEC320 C13 to NEMA 5-15P, or IEC320 C13 to IEC320 C14, 6' long • High combined airflow of 160CFM provided by 6x Orion OD4028-12HBXC • Bi-Color LED alarm indicator lamp • Optional redundant 2nd power supply available • Redundant power switching is seamless and automatic • Tray power input may be from customers 12V DC supply using Center-Positive 2.1mm I.D. x 5.5mm O.D. DC barrel connector • Sturdy 16 Gauge Powder Coated Steel Construction
-------------	---

OAT615	Fan Tray with power supply and 6' cord with NEMA 5-15 plug
OAT615-IEC	Fan Tray with power supply and 6' cord with IEC320 C14 plug
OAT615-DUAL	Fan Tray with 2x power supplies, redundant configuration, including 6' cords with NEMA 5-15P plugs
OAT615-IEC-DUAL	Fan Tray with 2x power supplies, redundant configuration, including 6' cords with IEC320 C14 plugs
OAT615-PS:	Add-on power supply. Needed for OA615 Dual redundant capability. Includes 6' cord with NEMA 5-15P plug
OAT615-IEC-PS	Add-on power supply. Needed for OA615 Dual redundant capability. Includes 6' cord with IEC320 C14 plug



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Orion Fans:

[OAT615](#) [OAT615-DUAL](#) [OAT615-IEC](#) [OAT615-IEC-DUAL](#) [OAT615-IEC-PS](#) [OAT615-PS](#)