


# OD9238 Series - High Speed





DC Fan - 12V, Tachometer, PWM  
92x38mm (3.62" x 1.5")



Frame & Impeller	PBT, UL94V-O plastic	<b>Available Options:</b>  * Connection: Red (+) Black (-) White - Tachometer Open Collector Blue - PWM  UL 1430, 24AWG ~300mm  Weight: ~ 255 g	
Connection	4x Lead wires *		
Motor	Brushless DC, auto restart, polarity protected.		
Bearing System	Dual ball bearing		
Insulation Resistance	Min. 10M at 500VDC		
Dielectric Strength	1 minute at 500VAC / 1 second, max leakage 500 microamp		
Temperature Range	-20C ~ +70C		
Storage Temperature	-40C ~ +80C		
Life Expectancy	50000 hours (40C)		

Part Number	OD9238-12HHBXC10A
Nominal Voltage	12 VDC
Nominal Current	3.5 A
Real Power	42 W
Rated Speed (RPM)	8000
Airflow (CFM)	174
Noise Level (dB)	68
Max. Static Pressure	1.7" H <sub>2</sub> O



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Orion Fans:

[OD9238-12HHBXC10A](#)