

Typical Specifications



Items	Specifications
Rated power	0.025W
Maximum operating voltage	5V DC
Operating travel	Each direction $2^{+0.2}_0$ mm
Operating force	0.75 ± 0.3 N
Operating life	2,000,000 cycles

Product Line

Product No.	Lever return mechanism	Center-push	Total resistance (kΩ)	Resistance taper	Minimum order unit (pcs.)	
					Japan	Export
RKJXU1210006	With	Without	5	B	2,000	2,000

Packing Specifications


Tray

Number of packages (pcs.)		Export package measurements (mm)
1 case / Japan	1 case / export packing	
2,000	2,000	540×360×230


Dimensions

Unit:mm

Style




Circuit Diagram



Multi Control Devices

List of Varieties

*Products marked with a  are not recommended for new designs

Type		Potentiometer type				
Series		RKJXK	RKJXV	RKJX2	RKJXU	
Photo						
Dimensions (typical value) (mm)	W	20.7	17.8	13.7	18.6	
	D	25.4	21.3	14.6	24.3	
	H	12.9	11.2	7.8	5.2	
Shaft material		Metal	Resin			
Directional resolution		Continuous				
Directional operating feeling (tactile feeling)		Without				
Lever return mechanism		With / Without	With			
Center-push switch		With / Without		With	Without	
Encoder		Without				
Operating temperature range		-10℃ to +70℃		-10℃ to +50℃	-10℃ to +70℃	
Operating life	Directional operation	100,000 cycles	2,000,000 cycles	2,000,000 cycles	2,000,000 cycles	
	Center-push	100,000 cycles	500,000 cycles	500,000 cycles	—	
Automotive use		—	—	—	—	
Life cycle (availability)						
Electrical performance	Insulation resistance	100MΩ min. 250V DC			—	
	Voltage proof	250V AC for 1 minute			—	
	Slider noise	300mV p-p max. by JIS method		300mV p-p max.	300mV p-p max. by JIS method	
Mechanical performance	Directional operating force		8mN·m max. Without Lever return mechanism 6±4mN·m With Lever return mechanism	14±10mN·m	7 ⁺⁵ ₋₃ mN·m	0.75±0.3N
	Push operating force		5.2±2.6N	7.4±3N	6±2.5N	—
	Lever return precision		±5°			±0.1mm
	Actuator strength	Push / pull directions	50N min. (Push/Pull)	98N min. (Push), 50N min. (Pull)		100N min. (Push), 30N min. (Pull)
		Operating direction	0.3N·m	—		50N
Environmental performance	Cold		-30℃ 96h			
	Dry heat		80℃ 96h			
	Damp heat		60℃, 90 to 95%RH 96h			
Page		393			396	

Variable Resistor Type Multi Control Devices Soldering Conditions 397
 Variable Resistor Type Multi Control Devices Cautions 397

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alps Alpine:](#)

[RKJXU1210006](#)