


Data sheet

chainflex® CF78.UL



Control cable (Class 5.5.3.1) • For heavy duty applications • PUR outer jacket • Shielded
• Oil resistant and coolant-resistant • Flame retardant • PVC and halogen-free • Notch-resistant • Hydrolysis and microbe-resistant



Example image
For detailed overview please see design table

Cable structure

	Conductor	Finely stranded conductor consisting of bare copper wires (following DIN EN 60228).
	Core insulation	Mechanically high-quality TPE mixture.
	Core structure	Number of cores < 12: Cores wound in a layer with short pitch length. Number of cores ≥ 12: Cores wound in bundles which are then wound around a high tensile strength centre element, all with optimised short pitch lengths and directions. Especially low-torsion structure.
	Core identification	Black cores with white numbers, one green-yellow core.
	Inner jacket	TPE mixture adapted to suit the requirements in e-chains®.
	Overall shield	Bending-resistant braiding made of tinned copper wires. Coverage approx. 55 % linear, approx. 80 % optical
	Outer jacket	Low-adhesion, halogen-free, highly abrasion resistant PUR mixture, adapted to suit the requirements in e-chains® (following DIN EN 50363-10-2). Colour: Window-grey (similar to RAL 7040) Printing: black
	CFRIP®	Strip cables faster: a tear strip is moulded into the inner jacket Video ► www.igus.eu/CFRIP

„00000 m*** igus chainflex CF78.UL-.-.① --② -/V③ E310776

cRUus AWM Style 21223 VW-1 AWM I/II A/B 80°C ---V⑤ FT-1 DNV TAE00003X1

EAC CE UKCA RoHS-II conform www.igus.de +++ chainflex cable works +++

* **Length printing:** Not calibrated. Only intended as an orientation aid.
① / ② Cable identification according to Part No. (see technical table).
③ Printing of nominal voltage (see general electrical values).
④ / ⑤ Printing of the UL Style / Voltage (see certifications for details).
Example: ... chainflex **CF78.UL.05.04 (4G0.5)C 300 V/500 V** ...



Data sheet

chainflex® CF78.UL



Control cable (Class 5.5.3.1) • For heavy duty applications • PUR outer jacket • Shielded
• Oil resistant and coolant-resistant • Flame retardant • PVC and halogen-free • Notch-resistant • Hydrolysis and microbe-resistant

Dynamic information

	Bend radius	e-chain® linear flexible fixed	minimum 6.8 x d minimum 5 x d minimum 4 x d
	Temperature	e-chain® linear flexible fixed	-25 °C up to +80 °C -40 °C up to +80 °C (following DIN EN 60811-504) -50 °C up to +80 °C (following DIN EN 50305)
	v max.	unsupported gliding	10 m/s 5 m/s
	a max.		80 m/s²
	Travel distance		Unsupported travels and up to 100 m for gliding applications, Class 5

These values are based on specific applications or tests. They do not represent the limit of what is technically feasible.

Guaranteed service life according to guarantee conditions

Double strokes	5 million		7.5 million		10 million	
	< 10 m	≥ 10 m	< 10 m	≥ 10 m	< 10 m	≥ 10 m
Temperature, from/to [°C]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]
-25/-15	8.5	10	9.5	11	10.5	12
-15/+70	6.8	7.5	7.5	8.5	8.5	9.5
+70/+80	8.5	10	9.5	11	10.5	12

Minimum guaranteed service life of the cable under the specified conditions.
The installation of the cable is recommended within the middle temperature range.

Electrical information

	Nominal voltage	300/500 V (following DIN VDE 0298-3) Number of cores < 12: Cores < 0.5 mm²: 300 V (following UL) Cores ≥ 0.5 mm²: 1000 V (following UL) Number of cores ≥ 12: 1000 V (following UL)
	Testing voltage	2000 V (following DIN EN 50395)



Example image

Data sheet

chainflex® CF78.UL



Control cable (Class 5.5.3.1) • For heavy duty applications • PUR outer jacket • Shielded
• Oil resistant and coolant-resistant • Flame retardant • PVC and halogen-free • Notch-resistant • Hydrolysis and microbe-resistant

Properties and approvals

	UV resistance	Medium
	Oil resistance	Oil-resistant (following DIN EN 50363-10-2), Class 3
	Offshore	MUD-resistant following NEK 606 - status 2009
	Flame retardant	According to IEC 60332-1-2, Cable Flame, VW-1, FT1, FT2 / Horizontal Flame
	Silicone-free	Free from silicone which can affect paint adhesion (following PV 3.10.7 – status 1992)
	Halogen-free	Following DIN EN 60754
	UL verified	Certificate No. B129699: „igus 36-month chainflex cable guarantee and service life calculator based on 2 billion test cycles per year“
	UL/CSA AWM	Details see table UL AWM
	NFPA	Following NFPA 79-2018, chapter 12.9
	DNV-GL	Type approval certificate No. TAE00003X1
	EAC	Certificate No. RU C-DE.ME77.B.00300/19 (TR ZU)
	REACH	In accordance with regulation (EC) No. 1907/2006 (REACH)
	Lead-free	Following 2011/65/EC (RoHS-II/RoHS-III)
	Cleanroom	According to ISO Class 1. The outer jacket material of this series complies with CF77. UL05.12.D - tested by IPA according to standard DIN EN ISO 14644-1
	CE	Following 2014/35/EU
	UKCA	In accordance with the valid regulations of the United Kingdom (as at 08/2021)



Example image



Data sheet

chainflex® CF78.UL



Control cable (Class 5.5.3.1) ● For heavy duty applications ● PUR outer jacket ● Shielded
● Oil resistant and coolant-resistant ● Flame retardant ● PVC and halogen-free ● Notch-resistant ● Hydrolysis and microbe-resistant


Properties and approvals

UL/CSA AWM Details

Conductor nominal cross section [mm²]	Number of cores	UL style core insulation	UL style outer jacket	UL Voltage Rating [V]	UL Temperature Rating [°C]
0.5	4-9	11323	20940	1000	80
0.5	12-25	11323	21223	1000	80
0.75	3-7	11323	20940	1000	80
0.75	12-36	11323	21223	1000	80
1	3-7	11323	20940	1000	80
1	12-25	11323	21223	1000	80
1.5	3-42	11323	21223	1000	80
2.5	3-12	11323	21223	1000	80
4	4	11323	21223	1000	80

Typical lab test setup for this cable series

Test bend radius R	approx. 48 - 200 mm
Test travel S	approx. 1 - 15 m
Test duration	minimum 2 - 4 million double strokes
Test speed	approx. 0.5 - 2 m / s
Test acceleration	approx. 0.5 - 1.5 m / s²



Typical application areas

- For heavy duty applications, Class 5
- Unsupported travel distances and up to 100 m for gliding applications, Class 5
- Almost unlimited resistance to oil, Class 3
- No torsion, Class 1
- Indoor and outdoor applications with average sun radiation
- Machining units/machine tools, Storage and retrieval units for high-bay warehouses, Packaging industry, quick handling, refrigerating sector



igus 36-month chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



Example image

igus® chainflex® CF78.UL

Data sheet

chainflex® CF78.UL



Control cable (Class 5.5.3.1) ● For heavy duty applications ● PUR outer jacket ● Shielded
● Oil resistant and coolant-resistant ● Flame retardant ● PVC and halogen-free ● Notch-resistant ● Hydrolysis and microbe-resistant

Technical tables:

Mechanical information

Part No.	Number of cores and conductor nominal cross section [mm²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF78.UL.05.04	(4G0.5)C	8.0	38	77
CF78.UL.05.05	(5G0.5)C	8.0	45	91
CF78.UL.05.07	(7G0.5)C	9.5	59	115
CF78.UL.05.09	(9G0.5)C	11.0	77	143
CF78.UL.05.12	(12G0.5)C	12.5	92	202
CF78.UL.05.18	(18G0.5)C	14.5	146	248
CF78.UL.05.25	(25G0.5)C	16.0	168	354
CF78.UL.07.03	(3G0.75)C	8.0	42	79
CF78.UL.07.04	(4G0.75)C	8.5	49	96
CF78.UL.07.05	(5G0.75)C	9.5	61	112
CF78.UL.07.07	(7G0.75)C	10.5	83	151
CF78.UL.07.12	(12G0.75)C	13.5	136	249
CF78.UL.07.18	(18G0.75)C	15.5	194	354
CF78.UL.07.36	(36G0.75)C	22.0	390	702
CF78.UL.10.03	(3G1.0)C	8.5	50	96
CF78.UL.10.04	(4G1.0)C	9.0	62	112
CF78.UL.10.05	(5G1.0)C	9.5	74	129
CF78.UL.10.07	(7G1.0)C	11.0	104	176
CF78.UL.10.12	(12G1.0)C	14.5	166	300
CF78.UL.10.18	(18G1.0)C	17.0	240	407
CF78.UL.10.25	(25G1.0)C	20.0	325	545
CF78.UL.15.03	(3G1.5)C	9.5	68	122
CF78.UL.15.04	(4G1.5)C	10.0	86	145
CF78.UL.15.05	(5G1.5)C	9.5	108	159
CF78.UL.15.07 ¹⁷⁾	(7G1.5)C	11.5	144	217
CF78.UL.15.12	(12G1.5)C	16.0	233	387
CF78.UL.15.18	(18G1.5)C	19.0	346	541
CF78.UL.15.25	(25G1.5)C	22.5	464	724
CF78.UL.15.36	(36G1.5)C	26.5	663	1095
CF78.UL.15.42 ¹¹⁾	(42G1.5)C	29.5	820	1296

Note: The given outer diameters are maximum values and may tend toward lower tolerance limits.
G = with green-yellow earth core x = without earth core



igus 36-month chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



Data sheet

chainflex® CF78.UL



Control cable (Class 5.5.3.1) ● For heavy duty applications ● PUR outer jacket ● Shielded
● Oil resistant and coolant-resistant ● Flame retardant ● PVC and halogen-free ● Notch-resistant ● Hydrolysis and microbe-resistant

Technical tables:

Mechanical information

Part No.	Number of cores and conductor nominal cross section [mm²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF78.UL.25.03	(3G2.5)C	10.0	106	174
CF78.UL.25.04	(4G2.5)C	11.5	140	203
CF78.UL.25.05	(5G2.5)C	12.0	166	235
CF78.UL.25.07 ¹⁷⁾	(7G2.5)C	14.5	230	334
CF78.UL.25.12	(12G2.5)C	19.0	382	585
CF78.UL.40.04	(4G4.0)C	13.0	203	328

¹¹⁾ Phase-out model

¹⁷⁾ When using the cables with „7G1.5mm²“ and „G2.5mm²“ minimum bend radius must be 17.5xd with gliding travel distance ≥ 5m.

Electrical information

Conductor nominal cross section [mm²]	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2) [Ω/km]	Max. current rating at 30 °C [A]
0.5	39	10
0.75	26	14
1	19.5	17
1.5	13.3	21
2.5	8	30
4	4.95	41

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.



igus 36-month chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



Example image

igus® chainflex® CF78.UL

Data sheet

chainflex® CF78.UL



Control cable (Class 5.5.3.1) • For heavy duty applications • PUR outer jacket • Shielded
 • Oil resistant and coolant-resistant • Flame retardant • PVC and halogen-free • Notch-resistant • Hydrolysis and microbe-resistant

Design table

Part No.	Number of cores	Core design	Part No.	Number of cores	Core design
CF78.UL.XX.03	3		CF78.UL.XX.12	4x3	
CF78.UL.XX.04	4		CF78.UL.XX.18	6x3	
CF78.UL.XX.05	5		CF78.UL.XX.25	5x5	
CF78.UL.XX.07	7		CF78.UL.XX.36	6x6	
CF78.UL.XX.09	9		CF78.UL.XX.42	7x6	



igus 36-month chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



Example image

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[igus:](#)

<u>CF78.UL.15.42</u>	<u>CF78.UL.25.04</u>	<u>CF78.UL.10.05</u>	<u>CF78.UL.15.12</u>	<u>CF78.UL.05.05</u>	<u>CF78.UL.10.18</u>	<u>CF78.UL.05.12</u>
<u>CF78.UL.07.04</u>	<u>CF78.UL.25.07</u>	<u>CF78.UL.07.36</u>	<u>CF78.UL.15.36</u>	<u>CF78.UL.25.03</u>	<u>CF78.UL.05.18</u>	<u>CF78.UL.15.04</u>
<u>CF78.UL.15.05</u>	<u>CF78.UL.07.05</u>	<u>CF78.UL.05.09</u>	<u>CF78.UL.05.25</u>	<u>CF78.UL.10.04</u>	<u>CF78.UL.10.12</u>	<u>CF78.UL.15.25</u>
<u>CF78.UL.15.18</u>	<u>CF78.UL.15.03</u>	<u>CF78.UL.07.18</u>	<u>CF78.UL.10.03</u>	<u>CF78.UL.10.25</u>	<u>CF78.UL.05.07</u>	<u>CF78.UL.07.03</u>
<u>CF78.UL.05.04</u>	<u>CF78.UL.07.12</u>	<u>CF78.UL.25.05</u>	<u>CF78.UL.25.12</u>	<u>CF78.UL.07.07</u>	<u>CF78.UL.40.04</u>	<u>CF78.UL.10.07</u>
<u>CF78.UL.15.07</u>						