

# XS212SAPAM12

Inductive proximity sensors XS, inductive sensor XS2 M12, L61mm, stainless, Sn7mm, 12...24 VDC, M12



## Main

|                                    |                                                               |
|------------------------------------|---------------------------------------------------------------|
| Range of Product                   | Telemecanique Inductive proximity sensors XS                  |
| Series name                        | Application                                                   |
| Sensor Type                        | Inductive proximity sensor                                    |
| Device Application                 | Food and beverage                                             |
| Market Segment                     | Pharmaceutical                                                |
| Sensor name                        | XS2                                                           |
| Sensor design                      | Cylindrical M12                                               |
| Size                               | 61 mm                                                         |
| Body type                          | Fixed                                                         |
| Detector flush mounting acceptance | Non flush mountable                                           |
| Material                           | Stainless steel                                               |
| Type of output signal              | Discrete                                                      |
| Wiring Technique                   | 3-wire                                                        |
| [Sn] nominal sensing distance      | 0.28 in (7 mm)                                                |
| Discrete output function           | 1 NO                                                          |
| Output circuit type                | DC                                                            |
| Discrete output type               | PNP                                                           |
| Electrical connection              | Male connector M12, 4 pins                                    |
| [Us] rated supply voltage          | 12...24 V DC reverse polarity protection                      |
| Switching capacity in mA           | <= 200 mA overload and short-circuit protection               |
| IP degree of protection            | IP67 conforming to IEC 60529<br>IP69K conforming to DIN 40050 |

## Complementary

|                        |                               |
|------------------------|-------------------------------|
| Thread type            | M12 x 1                       |
| Detection face         | Frontal                       |
| Front material         | PPS                           |
| Enclosure Material     | Stainless steel 316 L         |
| Sensing range          | > 0.16...0.31 in (> 4...8 mm) |
| Operating zone         | 0.00...0.22 in (0...5.6 mm)   |
| Differential travel    | 1...15% of Sr                 |
| Status LED             | Output state 1 LED yellow)    |
| Supply voltage limits  | 10...36 V DC                  |
| Switching frequency    | <= 2500 Hz                    |
| Maximum voltage drop   | <2 V closed)                  |
| Current consumption    | <= 10 mA no-load              |
| Maximum delay first up | 10 ms                         |
| Maximum delay response | 0.2 ms                        |
| Maximum delay recovery | 0.2 ms                        |
| Marking                | CE                            |
| Threaded length        | 1.46 in (37 mm)               |
| Length                 | 2.40 in (61 mm)               |
| Net Weight             | 0.08 lb(US) (0.035 kg)        |

## Environment

|                                       |                                         |
|---------------------------------------|-----------------------------------------|
| Product Certifications                | CSA<br>UL                               |
| Ambient Air Temperature for Operation | -13...185 °F (-25...85 °C)              |
| Ambient Air Temperature for Storage   | -40...185 °F (-40...85 °C)              |
| Vibration resistance                  | 25 gn +/- 2 mm 10...55 Hz)IEC 60068-2-6 |
| Shock resistance                      | 50 gn 11 ms IEC 60068-2-27              |

## Ordering and shipping details

|                   |                          |
|-------------------|--------------------------|
| Category          | 22486-SENSORS, PROXIMITY |
| Discount Schedule | DS2                      |
| GTIN              | 3389119113137            |
| Returnability     | Yes                      |
| Country of origin | FR                       |

## Packing Units

|                              |                  |
|------------------------------|------------------|
| Unit Type of Package 1       | PCE              |
| Number of Units in Package 1 | 1                |
| Package 1 Height             | 1.69 in (4.3 cm) |
| Package 1 Width              | 2.56 in (6.5 cm) |
| Package 1 Length             | 3.74 in (9.5 cm) |
| Package 1 Weight             | 1.06 oz (30.0 g) |
| Unit Type of Package 2       | S01              |
| Number of Units in Package 2 | 22               |
| Package 2 Height             | 5.91 in (15 cm)  |
| Package 2 Width              | 5.91 in (15 cm)  |
| Package 2 Length             | 15.75 in (40 cm) |
| Package 2 Weight             | 29.42 oz (834 g) |


## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                                   |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                                                                                                             |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                                                                 |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                                                                                                    |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                               |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                               |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                                     |
| Circularity Profile        | <a href="#">End Of Life Information</a>                                                                                                                                                                                                                                                                                                                                           |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Dimensions




(1) : LED

---

Minimum Mounting Distances in mm


---

Side by side




$e (1) \geq 48 \text{ mm}/1.89 \text{ in.}$

Face to face



$e (2) \geq 84 \text{ mm}/3.31 \text{ in.}$

Facing a metal object



$e (3) \geq 21 \text{ mm}/0.83 \text{ in.}$

(1) Metal

(2) Object to be detected

## Wiring Schemes

M12 connector



PNP



1 : (+)

2 : Not connected

3 : (-)

4 : NO Output

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[XS212SAPAM12](#)