


Male-Male Hex Standoff



Create a part number:

Length		Material		Finish
FCXXXX		XX		XX

Part Number						
✓ FCXXXX	Thread A	Length B	Thread C	Length D	Hex E	
FC4726	440	3/16	440	3/16	1/4	
FC4727	440	3/16	632	1/4	1/4	
FC4728	632	1/4	632	1/4	1/4	
FC4729	632	1/4	832	3/8	1/4	
FC4730	832	3/8	832	3/8	1/4	
FC4731	832	3/8	1032	3/8	1/4	
FC4732	1032	3/8	1032	3/8	1/4	
FC4733	832	3/8	832	3/8	5/16	
FC4734	832	3/8	1032	3/8	5/16	
FC4735	1032	3/8	1032	3/8	5/16	

Material		
✓	Material Code (XX)	
	A	Aluminum
	B	Brass
	S	Steel
	SS	Stainless Steel

Tolerances
Unless otherwise Specified
 .xxx +/- .005
 .xx +/- .010
 Angular +/- 1 Degree
 Linear +/- .005
Break all sharp edges

Source Control Drawing:
 To be produced by
 Fascomp Electronic Hardware

✓	Compatible Finish	
	A, B, S, SS	0 - Plain
	B, S	5 - Nickel Plate (QQ-N-290)
	A	6 - Iridite #14 Gold (MIL-C-5541E)
	A	7 - Iridite Clear (MIL-C-5541E)
	A	9 - Alodine 1200
	B, S	12 - Zinc Clear (ASTM-B-633)
	B, S	16 - Electro Tin (MIL-T-10727 TYPE 1)
	SS	20 - Passivation (MIL-F-14072D)
	A	22 - Clear Anodize (MIL-A-8625-TYPE2) (Sulphuric) Hot Water Seal (Clear)
	A	24 - Black Anodize (MIL-A-8625)
	B, S, SS	26 - Black Oxide
	B, S	28 - Zinc Yellow (ASTM-B-633)



This document is the property of Fascomp Inc. and shall not be reproduced, distributed, or used as a basis for manufacturing without written permission from Fascomp Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fascomp:

[FC4726-SS](#) [FC4727-SS](#) [FC4728-S-12](#) [FC4728-SS](#) [FC4729-S-12](#) [FC4729-SS](#) [FC4726-A](#) [FC4726-S-12](#) [FC4727-A](#) [FC4727-S-12](#) [FC4728-A](#) [FC4729-A](#) [FC4735-SS](#) [FC4730-S-12](#) [FC4730-SS](#) [FC4731-A](#) [FC4731-S-12](#) [FC4731-SS](#) [FC4733-SS](#) [FC4734-A](#) [FC4734-S-12](#) [FC4734-SS](#) [FC4735-A](#) [FC4735-S-12](#) [FC4730-A](#) [FC4732-A](#) [FC4732-S-12](#) [FC4732-SS](#) [FC4733-A](#) [FC4733-S-12](#)