



## Part Number: D3C1415



### Electrical Specifications

|                        |                 |
|------------------------|-----------------|
| Frequency Range (GHz): | 14.0 – 15.0     |
| Isolation (dB):        | 23 MIN          |
| Insertion Loss (dB):   | 0.3 MAX         |
| VSWR:                  | 1.2:1 MIN       |
| Forward Power (W):     | 10 AVG<br>50 PK |


### Mechanical/Environmental Specifications

|                   |                            |
|-------------------|----------------------------|
| Connector Type:   | SMA                        |
| Connector Body:   | Passivated stainless steel |
| Connector Pin:    | Gold plated copper         |
| Load Body:        | Brass                      |
| Magnetic Shunt:   | Nickel plated CRS          |
| Operational Temp: | -30°C to +65°C             |
| Weight (oz)       | 0.9 MAX                    |

### D3C1415 Dimensions



### D3C1415-3 Dimensions



Dimensions are in inches  
Tolerance


XX ±0.03  
XXX ±0.010

| Type of Device                                                          | PN Suffix | Connector Configuration<br>Input / Output | PN Example |
|-------------------------------------------------------------------------|-----------|-------------------------------------------|------------|
| Single Junction Circulator<br>3-Port Device<br>Port 1 / Port 2 / Port 3 | No Dash   | Female / Female / Female                  | D3C1415    |
|                                                                         | -1        | Male / Female / Female                    | D3C1415-1  |
|                                                                         | -2        | Female / Male / Female                    | D3C1415-2  |
|                                                                         | -3        | Male / Male / Male                        | D3C1415-3  |
|                                                                         | -4        | Female / Female / Male                    | D3C1415-4  |
|                                                                         | -5        | Male / Female / Male                      | D3C1415-5  |
|                                                                         | -6        | Male / Male / Female                      | D3C1415-6  |
|                                                                         | -7        | Female / Male / Male                      | D3C1415-7  |



## MEASURED DATA

Part Number: D3C1415, P1→P2, P3 Terminated with 50Ω, +25°C



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DiTom:](#)

[D3C1415](#) [D3C1415-1](#) [D3C1415-2](#) [D3C1415-3](#) [D3C1415-4](#) [D3C1415-5](#) [D3C1415-6](#) [D3C1415-7](#)