



Part Number: D4I2327


Electrical Specifications

Frequency Range (GHz):	2.3 – 2.7
Isolation (dB):	40 MIN
Insertion Loss (dB):	0.8 MAX
VSWR:	1.25:1 MIN
Forward Power (W):	150 AVG 350 PK
Reflective Power (W):	2 AVG


Mechanical/Environmental Specifications

Connector Type:	SMA
Connector Body:	Passivated stainless steel
Connector Pin:	Gold plated copper
Load Body:	Brass
Magnetic Shunt:	Nickel plated CRS
Operational Temp:	-20°C to +65°C
Weight (oz)	5.5 MAX

D4I2327 Dimensions



D4I2327-3 Dimensions




Dimensions are in inches
Tolerance
XX ±0.03
XXX ±0.010

Type of Device	PN Suffix	Connector Configuration Input / Output	PN Example
Single and Dual Junction Isolator, 2-Port Device Input / Output	N/A	Female / Female	D4I2327
	-1	Male / Female	D4I2327-1
	-2	Female / Male	D4I2327-2
	-3	Male / Male	D4I2327-3



MEASURED DATA

Part Number: D4I2327, +25°C



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DiTom:](#)

[D4I2327](#) [D4I2327-1](#) [D4I2327-2](#) [D4I2327-3](#)