

## Transponder Coils (for RFID)

Our surface mount transponder coils (wire wound) series cover a wide range of electrical performances. Its length and cross section area are optimized for best sensitivity in the coil axis. Customized inductance values are available upon request.

**Applications** Used for wireless data transmission in low frequency RFID products, such as immobilizers, TPMS and keyless entry. Other industrial applications include access control and tracking devices.

### Technical Data

L – Value (rated inductance)	Measured with Bode 100 Vector Network Analyzer or equivalent at frequency $f_L$
Q – Factor (min)	Measured with Bode 100 Vector Network Analyzer or equivalent at frequency $f_Q$
SRF (min)	Measured with HP 8753ES Network Analyzer or equivalent
DCR (max)	Measured at 25°C
Operating Temperature	-40°C to +150°C (Including component self-heating) For FTC from -40°C to +125°C
Pad Metallization	Gold flash as top layer, except ZASL with tin plating
Wire termination	Spot welding, except ZASL
Recommended soldering method	<a href="#">Reflow</a>
Moisture Sensitivity Levels (MSL)	MSL Level 1, indicating unlimited floor life at $\leq 30^\circ\text{C}$ / 85% relative humidity
Solderability	Using lead free solder (Sn 99.9) at $260^\circ\text{C} \pm 5^\circ\text{C}$ for $5 \pm 0.5$ seconds, min 90% solder coverage of metallization Standard: IEC 68-2-20 (Ta)
Resistance to Soldering Heat	Resistant to $260^\circ\text{C} \pm 5^\circ\text{C}$ for $10 \pm 1$ seconds Standard: IEC 68-2-20 (Tb)
Resistance to Solvent	Resistant to Isopropyl alcohol for $5 \pm 0.5$ minutes at $23^\circ\text{C} \pm 5^\circ\text{C}$ Standard: IEC 68-2-45
Climatic Test	Defined by the following standards IEC 68-2-1 for Cold test: $-40^\circ\text{C}$ for 96 hours IEC 68-2-2 for Dry heat test: $125^\circ\text{C}$ for 96 hours IEC 60068-2-78 for Humidity test: $40^\circ\text{C}$ at RH 95% for 4 days
Thermal Shock Test	Temperature cycle: $-40^\circ\text{C}$ to $+125^\circ\text{C}$ to $-40^\circ\text{C}$ Max/Min temperature duration: 15 min Temperature transition duration: 5 min Cycles: 25 Standard: MIL-STD-202G
Adhesion of Soldered Component (Shear Test)	Components withstand a pushing force of 10N for $10 \pm 1$ seconds Standard: IEC 60068-2-21, method Ue3
Mechanical Shock	Mil-Std 202 Method 213 Condition C 3 axis, 6 times, total 18 shocks 100 G, 6 ms, half-sine
Vibration	Mil-Std 202 Method 204 20 mins at 5G 10 Hz to 2000 Hz 12 cycles each of 3 orientations

Technical Data & Packing Specification

**Ordering Code** Example: 4408AF-371X-YY

**4408 AF - 371 X - YY** → **4408AF-371K-04**  
(Case Size) (Core Type) (Inductance Value) (Tolerance) (Packing Code)


Case Size - 1210, 1812, 4408, ZASL

Core Type - FTC (Ferrite), AFTC (Ceramic & Ferrite), AF/AQ (Ceramic & Ferrite), ZASL (Ferrite)

Tolerances - J (5%), K (10%)

Packing Code - 01, 04, 08 (Taped / Reel)

### Packing Specification



Type	Packing Code	D	D <sub>0</sub>	d	d <sub>1</sub>	B	b	W	P	P <sub>0</sub>	P <sub>1</sub>	K <sub>0</sub>	T
1210 FTC	01	180	1.55	60	13	18.4	13.7	12	8	4	2	2.55	0.30
1210 FTC	04	330	1.55	100	13	18.4	12.4	12	8	4	2	2.55	0.30
1812 AFTC	01	180	1.50	60	13	18.4	15.4	12	8	4	2	4.0	0.28
1812 AFTC	04	330	1.50	100	13	18.4	12.4	12	8	4	2	3.7	0.35
4408 AF/AQ	04/08	330	1.55	100	13	30.4	24.5	24	8	4	2	2.7	0.30
ZASL	04	330	1.50	100	13	30.4	24.4	24	12	4	2	3.6	0.30

## FASTRON's Component Key Characteristics



Approved according to AEC-Q200



Approved according to AEC-Q200 with High Temperature



Suitable for High Temperature



Part is RoHS conform and Halogen free



Mechanical Shock and Vibration Proof



Designed for High Q-values



Exceptionally High Q-values





Optimized for High Currents




Optimized for High Voltages

# 4408 AF


Transponder Coil



Typical Ls vs Frequency (f)



Typical Q vs Frequency (f)



Part No	Inductance L (mH)	f <sub>L</sub> (kHz)	Tol ± (%)	Q min	f <sub>Q</sub> (kHz)	SRF ref (kHz)	DCR max (Ω)	Sensitivity (mV/μT)
4408AF-371K-YY	0.37	125	10	27	125	1200	6.4	9
4408AF-401K-YY	0.40	125	10	27	125	1100	6.8	9
4408AF-421K-YY	0.42	125	10	27	125	1100	8.1	9
4408AF-511K-YY	0.51	125	10	27	125	1000	8.5	11
4408AF-701K-YY	0.70	125	10	30	125	821	12	15
4408AF-901K-YY	0.90	125	10	28	125	760	13.9	19
4408AF-102K-YY	1.00	125	10	28	125	710	15	19
4408AF-112K-YY	1.08	125	10	31	125	710	15	19
4408AF-122K-YY	1.20	125	10	30	125	710	18	24
4408AF-132K-YY	1.34	125	10	30	125	700	20	25
4408AF-202K-YY	1.97	125	10	30	125	630	29.7	32
4408AF-242K-YY	2.38	125	10	32	125	560	30.8	40
4408AF-272K-YY	2.66	125	10	35	125	530	35.2	40
4408AF-292K-YY	2.89	125	10	35	125	530	35.2	41
4408AF-332K-YY	3.30	125	10	35	125	450	48	46
4408AF-342K-YY	3.45	125	10	29	125	430	60	48
4408AF-412K-YY	4.15	125	10	29	125	400	70	57
4408AF-472K-YY	4.70	125	10	29	125	380	70	63
4408AF-482K-YY	4.80	125	10	29	125	380	80	64
4408AF-492K-YY	4.90	125	10	29	125	380	80	66
4408AF-562K-YY	5.60	125	10	28	125	350	80	75
4408AF-682K-YY	6.80	125	10	28	125	345	95	98
4408AF-702K-YY	7.00	125	10	30	125	340	100	99
4408AF-712K-YY	7.10	125	10	30	125	340	100	100
4408AF-722K-YY	7.20	125	10	30	125	335	86.4	104
4408AF-812K-YY	8.10	125	10	28	125	310	125	119
4408AF-902K-YY	9.00	125	10	28	125	310	111.6	141
4408AF-952K-YY	9.50	125	10	28	125	310	111.6	172
4408AF-103K-YY	10.0	125	10	30	125	310	111.6	175
4408AF-133K-YY	13.5	125	10	30	125	200	130	246
4408AF-163K-YY	16.2	125	10	30	125	200	175	364

**Core Material:** Ceramic & Ferrite

Revision date: 24 Feb 2022

**SPQ:** Taped / Reel 1000 [-08]  
3000 [-04]

**Remarks:** - Unlisted inductance values available upon request.  
- 2% and 5% tolerance available upon request.

(for RFID)

Transponder Coils

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Fastron:

[4408AF-712J-04](#) [4408AF-901J-04](#) [4408AF-332J-04](#) [4408AF-242J-04](#) [4408AF-412J-04](#) [4408AF-492J-04](#) [4408AF-202J-04](#) [4408AF-812J-04](#) [4408AF-401J-04](#) [4408AF-112J-04](#) [4408AF-103J-08](#) [4408AF-112J-08](#) [4408AF-202J-08](#) [4408AF-242J-08](#) [4408AF-332J-08](#) [4408AF-401J-08](#) [4408AF-412J-08](#) [4408AF-472J-08](#) [4408AF-482J-08](#) [4408AF-492J-08](#) [4408AF-562J-08](#) [4408AF-682J-08](#) [4408AF-702J-08](#) [4408AF-712J-08](#) [4408AF-722J-08](#) [4408AF-812J-08](#) [4408AF-901J-08](#) [4408AF-902J-08](#) [4408AF-562J-04](#) [4408AF-902J-04](#) [4408AF-722J-04](#) [4408AF-702J-04](#) [4408AF-482J-04](#) [4408AF-472J-04](#) [4408AF-682J-04](#) [4408AF-103J-04](#) [4408AF-103K-08](#) [4408AF-112K-08](#) [4408AF-122K-08](#) [4408AF-132K-08](#) [4408AF-133K-08](#) [4408AF-163K-08](#) [4408AF-712K-08](#) [4408AF-722K-08](#) [4408AF-812K-08](#) [4408AF-901K-08](#) [4408AF-902K-08](#) [4408AF-952K-08](#) [4408AF-492K-08](#) [4408AF-511K-08](#) [4408AF-562K-08](#) [4408AF-682K-08](#) [4408AF-701K-08](#) [4408AF-702K-08](#) [4408AF-371K-08](#) [4408AF-401K-08](#) [4408AF-412K-08](#) [4408AF-421K-08](#) [4408AF-472K-08](#) [4408AF-482K-08](#) [4408AF-202K-08](#) [4408AF-242K-08](#) [4408AF-272K-08](#) [4408AF-292K-08](#) [4408AF-332K-08](#) [4408AF-342K-08](#) [4408AF-122K-04](#) [4408AF-511K-04](#) [4408AF-133K-04](#) [4408AF-133J-04](#) [4408AF-712K-04](#) [4408AF-952J-04](#) [4408AF-163J-04](#) [4408AF-421J-04](#) [4408AF-952K-04](#) [4408AF-292J-04](#) [4408AF-242K-04](#) [4408AF-272J-04](#) [4408AF-412K-04](#) [4408AF-421J-08](#) [4408AF-132J-04](#) [4408AF-122J-04](#) [4408AF-812K-04](#) [4408AF-482K-04](#) [4408AF-722K-04](#) [4408AF-342J-08](#) [4408AF-492K-04](#) [4408AF-901K-04](#) [4408AF-292K-04](#) [4408AF-132K-04](#) [4408AF-371J-08](#) [4408AF-511J-04](#) [4408AF-421K-04](#) [4408AF-342J-04](#) [4408AF-163K-04](#) [4408AF-472K-04](#) [4408AF-163J-08](#) [4408AF-701J-04](#) [4408AF-701K-04](#) [4408AF-952J-08](#)