

Pluggable Inductors (Pin Type Coils)

FASTRON's pluggable inductors offer a wide range of inductance values from 1μH to 150 000μH, a high Q and also suitable for high currents and high voltages. They come in shielded, tube and cap versions able to protect the winding. They are available in reel packaging and ammpack.

Applications Applied in DC-DC converters and all types of electronic instruments, such as digital amplifier LPF and signal filtering applications.

Technical Data

L – Value (rated inductance)	Measured with Bode 100 Vector Network Analyzer or equivalent at frequency f _L , 25°C ambient
Q – Factor (min)	Measured with Bode 100 Vector Network Analyzer or equivalent at frequency f _Q , 25°C ambient
SRF (min)	≥ 40 MHz measured with HP8753ES Network Analyzer or equivalent at 25°C ambient < 40 MHz measured with Bode 100 Vector Network Analyzer or equivalent at 25°C ambient
DCR (max)	Measured at 25°C ambient
Rated DC Current: I _{rms}	Max permissible DC Current (I) that causes a 40°C component temperature rise from 25°C ambient
Saturation Current: I _{sat}	I _{sat} , max permissible DC bias at 25°C ambient that causes inductivity drop 10% (typ.) related to the unloaded inductivity
Operating Temperature	-55°C to +125°C (including component self-heating) : 05HCP, 05HCP/T, 07P, 07P/F, 09P, 09P/P, 11P, 11PHC, 07M, 07MFG, 07HCP/T, 07HCPLP/T, 07HVP/T, 09HCP/T, 09HVP/T & 14HVP/T -55°C to +150°C (including component self-heating): 07HCP, 07HCPLP, 07HVP, 09HCP, 09HVP & 14HVP
Recommended Soldering Method	Wave
Moisture Sensitivity Levels (MSL)	MSL Level 1, indicating unlimited floor life at ≤ 30°C / 85% relative humidity
Solderability	Using lead free solder (Sn 99.9) at 260°C ± 5°C for 5 ± 0.5 seconds, min 90% solder coverage of metallization Standard: IEC 68-2-20 (Ta)
Resistance to Soldering Heat	Resistant to 260°C ± 5°C for 10 ± 1 seconds Standard: IEC 68-2-20 (Tb)
Resistance to Solvent	Resistant to isopropyl alcohol for 5 ± 0.5 minutes at 23°C ± 5°C Standard: IEC 68-2-45
Climatic Test	Defined by the following standards: IEC 68-2-1 for cold test: -55°C for 96 hours IEC 68-2-2 for dry heat test: +85°C for 96 hours: Pluggable, 05HCP, 05HCP/T, 07HCP/T, 07HVP/T, 07HCPLP, 09HCP/T, 09HVP/T & 14HVP/T +150°C for 96 hours: 07HCP, 07HVP, 07HCPLP, 09HCP, 09HVP & 14HVP IEC 60068-2-78 for humidity test: 40°C at RH 95% for 4 days
Thermal Shock Test	Temperature cycle: -55°C to +85°C to -55°C: Pluggable, 05HCP, 05HCP/T, 07HCP/T, 07HVP/T, 07HCPLP, 09HCP/T, 9HVP/T & 14HVP/T -55°C to +150°C to -55°C: 07HCP, 07HVP, 07HCPLP, 09HCP, 09HVP & 14HVP Max/Min temperature duration: 15 minutes Temperature transition duration: 5 minutes Cycles: 25 Standard: MIL-STD-202G
Tensile Strength of Leads (Pull Test)	Components withstand a pulling force of 10N for 10 ± 1 second For 05HCP, 05HCP/T: Components withstand a pulling force of 5N for 10 ± 1 second IEC 60068-2-21 (Ua ₁)
Mechanical Shock	Mil-Std 202 Method 213 Condition C 3 axis, 6 times, total 18 shocks 100 G, 6 ms, half-sine
Vibration	Mil-Std 202 Method 204 20 mins at 5G 10 Hz to 2000 Hz 12 cycles each of 3 orientations

Remarks : Above technical data is for non-shielded type only.

Ordering Code Example: 09P-101X-YY

09P - 101 X - YY → 09P-101K-51
(Model) (Inductance Value) (Tolerance) (Packaging Code)

Core Type - Ferrite






Tolerances - J (5%), K (10%), M (20%)

Packaging Code - 50 (Loose in Box) / (Tray / Box), 51 (Taped / Reel)

Pluggable Inductors (Pin Type Coils)

**Packaging
Specification**

Reel Taping
Packaging code: 51



*according to IEC 286

Series	H max	Ho	H1 max	P	Fig
07P	12.5	16	28	5	1
07P/F	10.5	18	32.2	3.5	3
09P	12.5	18	32.2	5	2
09P/F	13.4	18	32.2	5	3
07HCP & 07HVP	10	18	32.2	5	4
07HCP/T & 07HVP/T	10.5	18	32.2	5	5
11P / 11PHC	15	18	34	5	2
05HCP	7.5	18	28.5	2.5	4
05HCP/T	7.5	18	28.5	2.5	5
07HCPLP	8.0	18	29.0	5	4
07HCPLP/T	8.0	18	29.0	5	5

FASTRON's Component Key Characteristics



Approved according to AEC-Q200



Approved according to AEC-Q200 with High Temperature



Suitable for High Temperature



Part is RoHS conform and Halogen free



Mechanical Shock and Vibration Proof



Designed for High Q-values



Exceptionally High Q-values



Optimized for High Currents







Optimized for High Voltages

07M

Shielded

Also available in 3.5mm pitch (**07MFG**)



Part No	Inductance L (mH)	f_L (MHz)	Tol $\pm$ (%)	Q min	f_Q (MHz)	DCR max (Ω)	Rated DC Current I _{max} (mA)
07M-102K-50	1.0	0.02	10	130	0.252	2.00	350
07M-152K-50	1.5	0.02	10	130	0.252	2.30	335
07M-182K-50	1.8	0.02	10	120	0.252	2.70	330
07M-222K-50	2.2	0.02	10	120	0.252	3.00	315
07M-332K-50	3.3	0.02	10	115	0.252	3.80	300
07M-392K-50	3.9	0.02	10	115	0.252	4.30	260
07M-472K-50	4.7	0.02	10	110	0.252	4.90	235
07M-682K-50	6.8	0.02	10	150	0.079	6.55	230
07M-103K-50	10	0.02	10	150	0.079	8.55	200
07M-153K-50	15	0.02	10	150	0.079	13.50	150
07M-223K-50	22	0.02	10	150	0.079	18.50	140
07M-273K-50	27	0.02	10	140	0.079	22.00	120
07M-333K-50	33	0.02	10	135	0.079	26.00	110
07M-393K-50	39	0.02	10	130	0.079	38.00	100
07M-473K-50	47	0.02	10	100	0.079	48.50	85
07M-563K-50	56	0.02	10	100	0.079	55.00	75
07M-683K-50	68	0.02	10	100	0.079	64.50	70
07M-823K-50	82	0.02	10	75	0.079	71.00	70

Core Material: Ferrite

Revision date: 03 Aug 2022

SPQ:	Packaging Form	Loose / Box
	Radial	250 [-50]

Remarks: - Also available with shorter leads.

- No cleaning on 07M and 07MFG is recommended once assembled on the PCB.
- Manual soldering is recommended for models 07M and 07MFG.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fastron:

<u>07M-392K-50</u>	<u>07M-332K-50</u>	<u>07M-223K-50</u>	<u>07M-104K-50</u>	<u>07M-222K-50</u>	<u>07M-102K-50</u>	<u>07M-272K-50</u>	<u>07M-393K-50</u>
<u>07M-103K-50</u>	<u>07M-183K-50</u>	<u>07M-562K-50</u>	<u>07M-473K-50</u>	<u>07M-832K-50</u>	<u>07M-122K-50</u>	<u>07M-153K-50</u>	<u>07M-182K-50</u>
<u>07M-683K-50</u>	<u>07M-273K-50</u>	<u>07M-333K-50</u>	<u>07M-123K-50</u>	<u>07M-682K-50</u>	<u>07M-472K-50</u>	<u>07M-823K-50</u>	<u>07M-152K-50</u>
<u>07M-563K-50</u>	<u>07M-822K-50</u>	<u>07M-152J-50</u>	<u>07M-683J-50</u>	<u>07M-104J-50</u>	<u>07M-832J-50</u>	<u>07M-473J-50</u>	<u>07M-393J-50</u>
<u>07M-182J-50</u>	<u>07M-273J-50</u>	<u>07M-223J-50</u>	<u>07M-563J-50</u>	<u>07M-823J-50</u>	<u>07M-153J-50</u>	<u>07M-272J-50</u>	<u>07M-222J-50</u>
<u>07M-332J-50</u>	<u>07M-123J-50</u>	<u>07M-822J-50</u>	<u>07M-183J-50</u>	<u>07M-102J-50</u>	<u>07M-333J-50</u>	<u>07M-392J-50</u>	<u>07M-122J-50</u>
<u>07M-103J-50</u>	<u>07M-472J-50</u>	<u>07M-562J-50</u>	<u>07M-682J-50</u>				