



Main

Range of Product	Telemecanique Ultrasonic sensors XX
Sensor Type	Ultrasonic sensor
Series name	General purpose
Sensor name	XX3
Sensor design	Cylindrical M18
Detection system	Diffuse
[Sn] nominal sensing distance	0.12 ft (0.0381 m) fixed
Material	Plastic
Type of output signal	Discrete
Discrete output function	1 NO
Wiring Technique	4-wire
Discrete output type	PNP/NPN
[Us] rated supply voltage	12...24 V DC reverse polarity protection
Electrical connection	Male connector M12 4 pins
[Sd] sensing range	0.12...0.17 ft (0.038...0.0508 m)
Beam angle	10 °
IP degree of protection	IP67 conforming to IEC 60529

Complementary

Enclosure Material	PEI
Front material	Silicone
Thread type	M18 x 1
Supply voltage limits	10...28 V DC
[Sa] assured operating distance	0.12...0.17 ft (0.038...0.0508 m)
Maximum differential travel	0.50 in (12.7 mm)
Blind zone	0.00...1.25 in (0...31.8 mm)
Minimum size of detected object	Cylinder diameter 50.8 mm 15.52 ft (4.732 m)
Status LED	Supply on 1 LED green) Output state 1 LED amber)
Current Consumption	100 mA
Maximum switching current	100 mA overload and short-circuit protection
Maximum voltage drop	1 V
Maximum delay first up	20 ms
Maximum delay response	1.5 ms
Maximum delay recovery	1.5 ms
Marking	CE
Height	0.71 in (18 mm)
Width	0.71 in (18 mm)
Depth	3.76 in (95.5 mm)

Environment

Standards	IEC 60947-5-2
Product Certifications	UL cCSAus
Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Ambient Air Temperature for Storage	-40...176 °F (-40...80 °C)
Vibration resistance	+/-1 mm 10...55 Hz)IEC 60068-2-6
Shock resistance	30 gn in all 3 axes 11 ms IEC 60068-2-27
Resistance to electrostatic discharge	8 kV level 4 IEC 61000-4-2
Resistance to electromagnetic fields	9.14 V/m (10 V/m) level 3 IEC 61000-4-3
Resistance to fast transients	1 kV level 3 IEC 61000-4-4

Ordering and shipping details

Category	22490-SENSORS-ULTRASONIC (XX5,6)
Discount Schedule	DS2
GTIN	3389119621939
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.57 in (4.0 cm)
Package 1 Width	1.57 in (4.0 cm)
Package 1 Length	2.56 in (6.5 cm)
Package 1 Weight	1.41 oz (40.0 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[XX318AU08EKAM12](#)