



Representative Image

## Catalog No. TM42422R

Description: 225A 42CRT 3P4W 208Y/120V 10K IC 3R

UPC No 783164077063

Home > Load Centers > Load Centers

Main breaker load centers arrive with a main breaker installed for a convenient and swift install. Main breakers allow for the user to stop the flow of electricity in the load center, shutting off all the power in the residence. The TM42422R features spaces for 42, 1" breakers, a 225A main ampere rating, 3 phases, and an outdoor suitable enclosure.

### Descriptors

Category	Load Centers
GO Schedule	R7

### Specifications

Load Center Type	Standard
Input/Output Voltage	208Y/120V ac
Interrupting Capacity Rating	22
Amperage	225 A
Device type	Main Breaker
Enclosure	Outdoor
Phase	3 Phase
1" Space	42
1/2" Space	0
Feed	Top
Door	No
GSA Compliance	No
Circuit Breaker Style	Plug-In
NEMA Rating	NEMA 3R
Factory Installed Ground Kit	No
Enclosure Type	Outdoor, Surface Mount
Wires	4 Wire
Service & Voltage	3 Phase, 4 Wire, 208Y/120V ac

### Classifications

UL/CUL Listing	UL
----------------	----



## Publications

Title	Publication No.	Publication Type
<a href="#">Section 1 BuyLog: Load centers and associated circuit breakers</a>	DET1023	Application and Technical
Guide includes product features, photos, product number selection guide, knockout drawings, wiring diagrams, accessories and options list. Only available on-line.		

**Additional Documentation:** Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABB:](#)

[TM42422R](#)