

12 Channel Parallel Active Optical Cable 120Gbit/s CXP-CXP AOC

FEATURES

- Full Duplex 12 Channel 850nm Parallel Active Optical Cable
- Supports transmission rates up to 10.3Gbit/s per channel
- CXP-based Small Form-factor hot pluggable interface
- Supports Rx Pre-Emphasis
- EEPROM-based Serial-ID, accessible through two-wire Serial Interface
- 12ch 850nm VCSEL array
- 12ch PIN-detector array
- Helix type 24-fiber Multi-Mode Optical cable of up to 50m to allow bending in any direction.
- Fire-resistant OFNP (Optical Fiber Non-Conductive Plenum) rated cable
- Low power consumption: 2.2 Watts (typ.)
- Power class 4
- 0°C to +70°C operating case temperature
- Laser Class 1 IEC/CDRH compliant
- RoHS 6/6 compliant
- Angled boot cable exit option available



APPLICATIONS

- Infiniband transmission at 12x SDR, 12x DDR and 12x QDR
- Multi-channel 10GE transmission up to 12 channels

SUPPORTED STANDARDS

- 120Gbit/s Small Form-factor Hot-Pluggable CXP-interface



ORDERING INFORMATION

DESCRIPTION	PART NUMBER	LENGTH
CXP-CXP cable-straight cable exit	ICD120GVP2410-05	5 meters
CXP-CXP cable-straight cable exit	ICD120GVP2410-10	10 meters
CXP-CXP cable-straight cable exit	ICD120GVP2410-20	20 meters
CXP-CXP cable-straight cable exit	ICD120GVP2410-50	50 meters
CXP-CXP cable-angled boot cable exit	ICD120GVP2430-10	10 meters
CXP-CXP cable-angled boot cable exit	ICD120GVP2430-20	20 meters

For more information please contact: elxcommunications@fci.com

www.fciconnect.com/hsio

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI:](#)

[ICD120GVP2410-10](#) [ICD120GVP2410-50](#) [ICD120GVP2410-C0](#) [ICD120GVP241030](#) [ICD120GVP241040](#)
[ICD120GVP241060](#) [ICD120GVP241070](#) [ICD120GVP241080](#) [ICD120GVP241090](#) [ICD120GVP2410-20](#)
[ICD120GVP2410-60](#)