

9012GEW1

Pressure switch 9012G, fixed scale, 1 threshold, 13 to 425 PSIG



Main

Range of Product	9012G
Pressure sensor type	Electromechanical pressure switch
Pressure sensor name	9012G
Pressure Rating	425 psi (2930.27 kPa)
Maximum pressure	850 psi
Contacts type and composition	NC-NO, SPDT-DB, Form Z, snap action, silver nickel contacts
Controlled fluid	Hydraulic oil -40...250 °F (-40...121 °C)) Non-corrosive liquids Air Non-corrosive gas
Fluid connection type	0.25 inch 18 NPTF UL 508
Pressure switch type of operation	Detection of 1 single threshold
Scale type	Fixed
Local display	Without

Complementary

Range on decreasing pressure	13...425 psi (89.63...2930.27 kPa)
Approx fix differential at mid range	16 psi (110.32 kPa) +/- 2.5 % full scale
Cable entry	0.5 inch NPT conduit entrance
Terminal block type	4 screw terminals
Electrical connection	Screw-clamp terminals, AWG 22...AWG 12
Electrical circuit type	Control circuit
Local signalling	Without
Line Rated Current	3 A 240 V AC A600 NEMA rating designation 6 A 120 V AC A600 NEMA rating designation 0.27 A 250 V DC R300 NEMA rating designation 0.22 A 125 V DC R300 NEMA rating designation
Setting	Internal
Enclosure Material	Die cast aluminium alloy 380
Pressure actuator	Diaphragm nitrile (Buna-N)
Height	5.45 in (138.43 mm)
Depth	2.63 in (66.80 mm)
Width	3.5 in (88.90 mm)
Operating position	Any position
Materials in contact with fluid	Zinc plated steel Nitrile (Buna-N)
Short-circuit protection	10 A cartridge overload and short-circuit protection gL
Maximum operating rate	120 cyc/mn
Mechanical durability	5000000 cycles
Repeat accuracy	4 %
Net Weight	3 lb(US) (1.36 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Vibration resistance	2 gn 40...150 Hz)IEC 68-2-6
Shock resistance	50 gn IEC 58-2-27
Standards	CSA C22.2 No 14 UL 508 CSA C22.2 No 14
Product Certifications	UL listed file E12158 CCN NKPZ and CCN NTHT UL listed file E12158 CCN NKPZ and CCN NTHT CE
NEMA degree of protection	NEMA 4/4X/13 UL 50
Ambient Air Temperature for Operation	-10...185 °F (-23...85 °C)

Ordering and shipping details

Category	21522-9012 G INDUSTRIAL PRESSURE SWITCHES
Discount Schedule	CP7G
GTIN	785901024958
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24.13 in (61.29 cm)
Package 1 Width	9.50 in (24.13 cm)
Package 1 Length	61.29 in (155.677 cm)
Package 1 Weight	3.00 lb(US) (1.361 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[9012GEW1](#)