



LAN-1 Lan Cable Tester

The Amprobe LAN-1 Cable Tester is designed for testing opens, shorts and miswired cable installations. It is designed to work with various data cables and connectors. This cable tester provides a quick go / no-go LED display of the wiring and connection of item under test. You can either step through the test cable wiring one at a time or have the unit automatically pulse through the pin-outs and display the results.

- Test pin configuration for:
 - 10/100 base -T cable
 - 10 base-2 cable
 - RJ45 modular cables
 - AT&T 258A cable
 - EIA / TIA 568A/568B cables
 - Token Ring Cable
- Verify the cable wiring for continuity, opens, shorts or incorrect wiring
- Test installed cable on wall plate or the patch panels by using the Remote Termination module
- Perform Loopback Test or Remote Test
- Buzzer sound warning for error condition in cable
- Two sets of LED lights for Source and Test indication
- Maximum line length: > 300 meters
- Connector types: RJ45, BNC
- Unit ships with Remote Terminator, 1 ea RJ45 to female BNC cable, 1 ea RJ45 to male BNC cable, 1 ea 1 RJ45 to RJ45 cable, 1 ea female BNC to female BNC connector, 9 volt battery and Users Manual

No hassle warranty

No waiting.

No shipping charges.



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: \$500 MSLP limit)

LAN-1 Lan Cable Tester

Data Sheet

Specifications

General Specifications	
Display	18 LEDs: 9 Red and 9 Green, 9 LEDs on Remote module
Battery	Standard 9-volt battery, NEDA 1604A, JIS 006P, IEC 6F22
Battery life	Approx 20 hours. (Alkaline battery)
Low Battery Indicator	The LED indicator will not turn ON when BATT button is pushed
Operating environment	0 to 40°C (32 to 104°F), 10 to 70% RH
Storage temperature	-10 to 60°C (14 to 140°F), 10 to 90% RH
Altitude	2000m, indoor operation
Dimensions	130 x 56 x 38 mm (5.1 x 2.2 x 1.5 in.)
Weight	1.26 kg (0.6 lb)
Cable Continuity	
Maximum line length	> 300 meters
Connector types	RJ45, BNC

Agency Approvals & Certifications

CE - EMC	Conforms to EN61326-1. This product complies with requirements of the following European Community Directives: 89/336/EEC (Electromagnetic Compatibility) and 73/23/EEC (Low Voltage) as amended by 93/68/EEC (CE Marking). However, electrical noise or intense electromagnetic fields in the vicinity of the equipment may disturb the measurement circuit. Measuring instruments will also respond to unwanted signals that may be present within the measurement circuit. Users should exercise care and take appropriate precautions to avoid misleading results when making measurements in the presence of electronic interference.
----------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------



Amprobe® Test Tools
website: www.Amprobe.com
email: info@amprobe.com
Everett, WA 98203
Tel: 877-AMPROBE

Amprobe® Test Tools Europe
Amprobe Test Tools Europe
Beha-Amprobe GmbH
In den Engematten 14
79286 Glottertal, Germany
Tel.: +49 (0) 7684 8009 - 0

©2008 Amprobe Test Tools. All rights reserved.
7/2008 3358131 Rev A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AMPROBE:](#)

[LAN-1](#)