



## PRM-4 Phase Sequence and Motor Rotation Tester

- Identifies 3-phase sequence and open phase check
- Motor shaft rotation indication protected by CAT III circuitry
- CAT III 600V rated for both testing segments
- Meets current EN61010 safety requirements, CSA, EN61557-7
- Supplied with three CAT III rated color coded large alligator clips and test leads
- Zippered carrying case for portability

### No hassle warranty

*No waiting.*

*No shipping charges.*



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: \$500 MSLP limit)

#### Included Accessories

Test Leads (red, green, and blue) with alligator clips (TL-PRM-4), Soft Vinyl Case, Users Manual, 9 V Battery

#### Optional Accessories

TL-PRM-4 Replacement Test Leads  
FP900 Replacement Fuses



## PRM-4 Phase Sequence and Motor Rotation Tester

### General Specifications

Operating Environment	0 °C to 40 °C at <80 % R.H.
Power	Single standard 9 V battery NEDA 1604 JIS 006P IEC 6F22
Battery life	Approximately 200 hours typical with carbon-zinc battery
Low battery indication	The BATT LED does not come ON when TEST button is pressed
Dimensions (H x W x D)	153 mm x 72 mm x 35 mm (6.02 x 2.83 x 1.37 in)
Weight	Approximately 218 g (7 oz) including battery.
Environment	Indoor use
Altitude	2000 m (6561 ft.)
Overload protection	600 V ac
Agency Approvals	CE, cCSAus
Safety	Conforms to EN61010-1:2001 CAT III 600V, Pollution degree 2, Class 2 CSA 22.2 -1010-1 EN61557-7
EMC	Conforms to EN61326-1. This product complies with requirements of the following European Community Directives: 89/ 336/ EEC (Electromagnetic Compatibility) and 73/ 23/ EEC (Low Voltage) as amended by 93/ 68/ EEC (CE Marking). However, electrical noise or intense electromagnetic fields in the vicinity of the equipment may disturb the measurement circuit. Measuring instruments will also respond to unwanted signals that may be present within the measurement circuit. Users should exercise care and take appropriate precautions to avoid misleading results when making measurements in the presence of electronic interference.

### Electrical Specifications

Function	Range
<b>Phase Sequence</b>	
Input Voltage	3 phase to phase inputs 100 V ac to 600 V ac max.
Frequency	45 to 70 Hz
Operating Time	10 minutes ON maximum at 600 V ac 10 minutes OFF minimum at 600 V ac
3-Phase load	Approx. 7 mA per phase of ac power source
<b>Motor Rotation</b>	
Operating Time	10 minutes ON maximum 10 minutes OFF minimum.
Motor Rotation tester field	14 mA of 9 V battery

**Amprobe® Test Tools**  
 website: [www.Amprobe.com](http://www.Amprobe.com)  
 email: [info@amprobe.com](mailto:info@amprobe.com)  
 Everett, WA 98203  
 Tel: 877-AMPROBE

**Amprobe® Test Tools Europe**  
 In den Engematten 14  
 79286 Glottertal, Germany  
 Tel.: +49 (0) 7684 8009 - 0

©2008 Amprobe Test Tools. All rights reserved.  
 2/2008 3303533 Rev A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AMPROBE:](#)

[PRM-4](#)