


Model 1296 BNC (Male) To Double Stacking Binding Post Jack



FEATURES:

- Converts BNC based test instruments to double binding posts with banana jacks.
- Binding Posts can be vertically and horizontally stacked for test versatility.
- Wires, spade lugs, pin tip plugs and banana plugs can be attached by means of the insulated knurled thumb knob.
- Insulated thumb knob is captive to prevent misplacement.
- BNC features Nickel Plated, Beryllium Copper for tarnish resistance & long insertion life.
- BNC center contact is Gold Plated, Brass for low contact resistance
- BNC shell is plated for tarnish resistance.

MATERIALS:

BNC (Male): Body: Brass, Nickel Plated
Dielectric: PTFE

Center Contact: Brass, Gold Plated

Impedance: 50 Ohms

Insulation: ABS Molded to BNC (Male) and Binding Post Bodies, Color: Black

Marking: "1296 POMONA"

Binding Post: Body – Brass, Nickel Plated

Insulated Thumb Knob –

Polycarbonate, Color: One Black, One Red

RATINGS:

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled

voltage environments: 500 VRMS Max.

Operating Temperature: +50°C (+122°F) Max

ORDERING INFORMATION: Model 1296

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

1296#