


Model 1432
Banana Jack to Pin Tip Plug

Model 1432
Banana Jack to Pin Tip Plug



SCHEMATIC

Features

- Permits banana plug cords to be used with equipment having pin tip jacks.

Materials**Banana Jack:**

Material: Brass rod per ASTM B16-85, Temper H02.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 micro-inches.

Pin Tip Plug:

Body: Brass rod per ASTM B16-85, Temper H02.

Finish: Nickel plate per QQ-N-290, Class 2, 200/300 micro-inches.

Insulation:

Material: Polypropylene molded to Banana Plug and Pin Tip bodies.

Marking: "1432, POMONA ELECTRONICS, CALIF."

Specifications**Operating Voltage:**

Hands free usage in controlled voltage environments: 3000 Vrms maximum.

For CE compliance: not intended for hand-held use at voltages above 33 Vrms/70 Vdc.

Operating Temperature: +50°C (+122°F) Max.

Current: 5 Amperes

Ordering Information

Model: 1432-*

*=Color, -0 (Black), -2 (Red)

Ordering Example: 1432-2 (Color is Red)

Other colors are available upon request.

USA: Sales: 800-490-2361
Technical Support: technicalsupport@pomonatest.com
Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[1432-0](#) [1432-2](#) [1432-2#](#) [1432-0#](#)