



FEATURES:

- Provides rapid method for splicing cables.
- Reduces necessity of storing extra long cables.
- 4.2 (.166) dia. Banana Jacks.

MATERIALS:

Upper Conn: Double Banana Jack

Material: Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200 to 300 microinches.

Insulation: Polypropylene molded to Banana Jack bodies

Marking: "POMONA ELECTRONICS CALIF." "MODEL 1823."

Color: See Ordering Information

Lower Conn:

Same as Upper Conn.

RATINGS:

Operating Temperature: +55° C. (+131° F.) Max.

Operating Voltage: 5000 VDC.

Current: 15 Amperes

ORDERING INFORMATION: Model 1823-*

*= Color, -0 Black, -2 Red

Ordering Example: 1823-2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[1823-0](#) [1823-2](#)