



FEATURES:

- Adapts banana jack test instruments for BNC Cable Assemblies.
- Banana plug spring is nickel-plated Beryllium Copper and BNC spring is gold plated Beryllium Copper for low contact resistance and long insertion life.
- Schematic: BNC center contact to Banana Plug, BNC shell is a no connect.

MATERIALS:

BNC Female: Body – Brass, Nickel Plated, Female Spring – Beryllium Copper, Gold Plated.

Insulation: ABS, Color – Black, Marking: “1894 Pomona Electronics, Calif.”

Banana Plug: Body – Brass, Nickel Plated, Spring – Beryllium Copper, Nickel Plated

RATING:

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 500 VRMS Max.

Operating Temperature: +50°C (+122°F)

ORDERING INFORMATION: Model 1894

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

1894#