



MATERIALS:

Connector: BNC (F) to BNC (M)

Body: Tarnish Resistant Plating, Center Contact: Gold Plated Beryllium Copper

Solder Turret Terminal Screws: Steel 4 each #4-40

Shielded Housing: Die cast aluminum, Alloy A380 or A384.

Finish: Blue baked enamel per Federal Standard 595 #25109 over Phosphoric Etch per MIL-C-15328.

Cover: .040 thick aluminum 1100-H14

Finish: Clear anodized per MIL-A-8625.

Screws: 4 each 2-32 x 6.35 (1/4") Pan head, self-tapping. Steel

RATINGS:

Operating Voltage: Inner Conductor/Shield: 500 VRMS Max.

Operating Temperature: -55°C to +150°C

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 3752

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

3752