


Model 4294 Adapter, SMA Male To TNC Female



MATERIALS:

Body: Gold Plated Beryllium Copper,
 Male Contact - Gold Plated Brass,
 Female Contact - Gold Plated Beryllium Copper

Dielectric: Teflon per L-P-403

Finish: Body and Contacts - Gold plated per MIL-G-45204, Type II, Class 2

Marking: "Pomona 4294"

RATINGS:

Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 335VRMS Max.

Operating Temperature: -65°C (-85°F) to +165°C (+329°F)

Nominal Impedance: 50 Ohms

Frequency Range: 0-12.4 GHz.

ORDERING INFORMATION: Model 4294

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4294](#)