


Model 5090
BNC (F) to 2 Lug Triaxial (M) Adapter


Model 5090
BNC (F) to 2 Lug Triaxial (M) Adapter



TRIAIX (M)



BNC (F)



Features

- Provides an easy interface between a BNC (F) and a 2 Lug Triax (M).

Materials

Body:	Brass, Tarnish Resistant Nickel Plated
Dielectric:	PTFE per L-P-403
Center Contact:	Male – Brass, Gold Plated Female – Beryllium Copper, Gold Plated
Outer Contact:	Beryllium Copper, Tarnish Resistant
Marking:	“POMONA 5090” (optional)

Ratings

Voltage: For *CE compliance* and for personal safety, do not hold in hand when voltages exceed 30 Vrms/60 Vdc.
Maximum voltage for *hands free use* in controlled testing environments: 500 Vdc
Do not use on circuits where transient stresses can exceed the rated voltage.

Frequency Range: DC to 500 MHz

Ordering Information

Model: 5090
BNC (F)/2 LUG TRIAXIAL (M)

USA: Sales: 800-490-2361
Technical Support: technicalsupport@pomonatest.com
Fax: 425-446-5844
Europe: 31-(0) 40 2675 150 **International:** 425-446-5500
Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm),
.xxx = $\pm .005$ " (.127 mm). All specifications are to the latest revisions.
Specifications are subject to change without notice. Registered trademarks are
the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

5090#